

Eaton 259143

Catalog Number: 259143

Eaton Moeller series NZM - Molded Case Circuit Breaker. Switch-disconnector 3p 63A BG1

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM switch-disconnector	259143
	EAN
	4015082591434
Product Length/Depth	Product Height
88 mm	145 mm
Product Width	Product Weight
90 mm	0.842 kg
Compliances	Certifications
RoHS conform	IEC/EN 60947
	IEC

Product specifications

Type

Switch-disconnector

Special features

Main switch characteristics including positive drive to IEC/EN 60204 and VDE 0113.

Isolating characteristics to IEC/EN 60947-3 and VDE 0660.

Busbar tag shroud to VDE 0160 Part 100.

Rated current = rated uninterrupted current: 63 A

Application

Use in unearthed supply systems at 690 V

Amperage Rating

63 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

N1

Features

Version as main switch

Version as maintenance-/service switch

Version as emergency stop installation

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_N1](#)

Drawings

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-017.eps](#)

eCAD model

[ETN.N1-63](#)

Installation instructions

[eaton-circuit-breaker-switch-disconnector-nzmb-il01203004z.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CS-nzm1_3p](#)

[DA-CD-nzm1_3p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Ground mounting

Intermediate mounting

Distribution board installation

Built-in device fixed built-in technique

Fixed

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Equipment heat dissipation, current-dependent

4.52 W

Isolation

300 V AC (between the auxiliary contacts)

500 V AC (between auxiliary contacts and main contacts)

Rated short-time withstand current (I_{cw})

2 kA

Degree of protection

IP20 (basic protection type, in the area of the HMI devices)

Other

Direction of incoming supply

As required

Electrical connection type of main circuit

Frame clamp

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-40 °C

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110

Rated insulation voltage (Ui)

690 V

Rated operating frequency

50 Hz

Rated operating power at AC-23, 400 V

30 kW

Rated operating power at AC-3, 400 V

0 kW

Switch positions

I, +, 0

Lifespan, mechanical

20000 operations

Overvoltage category

III

Rated operational current

160 A (415 V AC-22/23A, making and breaking capacity)

160 A (690 V AC-22/23A, making and breaking capacity)

Degree of protection (IP), front side

IP40 (with insulating surround)

IP66 (with door coupling rotary handle)

IP20

Degree of protection (terminations)

IP00 (terminations, phase isolator and band terminal)

IP10 (tunnel terminal)

Number of poles

Three-pole

Terminal capacity (copper strip)

Max. 9 segments of 9 mm x 0.8 mm at box terminal

Min. 2 segments of 9 mm x 0.8 mm at box terminal

Handle color

Black

Lifespan, electrical

1000 operations at 400 V AC-23A

10000 operations at 400 V AC-1

7500 operations at 690 V AC-1
1000 operations at 415 V AC-23A
1000 operations at 690 V AC-23A
10000 operations at 415 V AC-1

Functions

Disconnectors/main switches
Interlockable
Voltage release optional

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Number of switches

1

Rated conditional short-circuit current (I_q)

0 kA

Rated conditional short-circuit current with back-up fuse

80 kA at 690 V
100 kA at 400/415 V
63 gG/gL

Rated conditional short-circuit current with downstream fuse

100 kA at 400/415 V
63 gG/gL
10 kA at 690 V

Rated operating voltage (U_e) at AC - max

690 V

Rated operational current for specified heat dissipation (I_n)

63 A

Rated permanent current at AC-21, 400 V

0 A

Rated permanent current at AC-23, 400 V

0 A

Rated short-time withstand current (t = 0.3 s)

2 kA

Rated short-time withstand current (t = 1 s)

2 kA

Switching power at 400 V

0 kW

Handle type

Rocker lever

Number of operations per hour - max

120

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

2.8 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

6000 V

Standard terminals

Box terminal

Optional terminals

Connection on rear. Screw terminal. Tunnel terminal

Short-circuit protective device fuses - max

125 A gL

Terminal capacity (copper busbar)

Min. 12 mm x 5 mm direct at switch rear-side connection

Max. 16 mm x 5 mm direct at switch rear-side connection

M6 at rear-side screw connection

Terminal capacity (copper solid conductor/cable)

10 mm² - 16 mm² (1x) direct at switch rear-side connection

6 mm² - 16 mm² (2x) direct at switch rear-side connection

10 mm² - 16 mm² (1x) at box terminal

16 mm² (1x) at tunnel terminal

6 mm² - 16 mm² (2x) at box terminal

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) at tunnel terminal

10 mm² - 16 mm² (1x) direct at switch rear-side connection

10 mm² - 16 mm² (2x) direct at switch rear-side connection

Terminal capacity (copper stranded conductor/cable)

25 mm² - 70 mm² (1x) direct at switch rear-side connection

Terminal capacity hint: Up to 95 mm² can be connected

depending on the cable manufacturer

10 mm² - 70 mm² (1x) at box terminal

25 mm² - 95 mm² (1x) at 1-hole tunnel terminal

25 mm² (2x) direct at switch rear-side connection

6 mm² - 25 mm² (2x) at box terminal

Terminal capacity (aluminum stranded conductor/cable)

25 mm² - 95 mm² (1x) at 1-hole tunnel terminal



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)