

The trusted value of OSRAM Digital Systems continues with Inventronics Global – where experience meets innovation.

## ETi DALI 25/220-240/500 LT2 L (PHASE OUT)

ICUTRONIC Intelligent – DALI (SELV) | Linear constant current LED driver – Dimmable



### Product family features

- Line frequency: 0 Hz | 50 Hz | 60 Hz
- Versatile scope of application due to output power range of up to 71.4 W
- Supply voltage: 220...240 V
- Available with output current range: up to 1,400 mA
- SELV driver

### Product family benefits

- Versatile SELV DALI driver up to 75 W due to flexible output characteristic
- Fully programmable via software (DALI Interface)
- Flexible current setting (RSet)
- Lifetime: up to 100,000 h (temperature at  $T_c = 65^\circ\text{C}$ , max. 10 % failure rate)
- High-quality dimming of 10...100 % by amplitude dimming
- No TouchDIM nor Corridor Function
- High quality of light thanks to <3% output ripple current
- High efficiency
- Low standby consumption  $\leq 0.5\text{ W}$
- Fulfill safety requirement due to overload, overtemperature, Hot Plug protection

Specifications are subject to changes without notice.

[www.inventronicsglobal.com](http://www.inventronicsglobal.com)

© 2024, Inventronics GmbH. All rights reserved. Inventronics is a licensee of the OSRAM brand. OSRAM is a trademark of ams OSRAM

[support@inventronicsglobal.com](mailto:support@inventronicsglobal.com)

### Areas of application

- Linear and area lighting
- Linear lighting for office, education, industry, storage areas and retail
- Installation in emergency lighting systems according to IEC 61347-2-13, appendix J, except those used in high-risk task areas, i.e. those systems must not be used in workplaces where operators and other occupants of the premises are involved in potentially dangerous processes or situations.
- Suitable for luminaires of protection class I


## Technical data

### Electrical data


Nominal input voltage	220...240 V
Mains frequency	0/50/60 Hz
Input voltage AC	198...264 V
Input voltage DC	176...276 V
Total harmonic distortion	< 20 %
Power factor $\lambda$	0.60C...0.95
Efficiency in full-load	86 % <sup>1)</sup>
Device power loss	3.0 W
Networked standby power	<0.50 W <sup>1)</sup>
Inrush current	$\leq$ 10 A
Max. ECG no. on circuit breaker 10 A (B)	30
Max. ECG no. on circuit breaker 16 A (B)	50
Surge capability (L-N)	1 kV
Surge capability (L/N-Ground)	2 kV
Nominal output voltage	20...51 V
U-OUT (working voltage)	< 60 V
Nominal output current	180...500 mA
Default output current	180 mA
Output current tolerance	$\pm$ 7 %
Output ripple current (100 Hz)	< 3 %
Output PSTLM	$\leq$ 1
Output SVM	$\leq$ 0.4
Output current LEDset open	180 mA
Nominal output power	3.6...25.5 W
Maximum output power	25.5 W

1) at 230 V, 50 Hz

### Typical Power Factor v Load




### Operating Window



ETI DALI 25 LT2 L Typical Power Factor vs. Load

ETI DALI 25 LT2 L Operating Window

### Typical THD v Load




### Typical Efficiency v Load 230 V 50 Hz



ETI DALI 25 LT2 L Typical THD Vs Load

ETI DALI 25 LT2 L Typical Efficiency vs. Load

## Dimensions & weight



Product weight	170.00 g
Length	280.0 mm
Width	30.0 mm
Height	21.0 mm
Mounting hole spacing, length	270.0 mm
Cable cross-section, input side	0.5...1.5 mm <sup>2</sup>
Cable cross-section, output side	0.5...1.5 mm <sup>2</sup>
Wire preparation length, input side	8.0...9.0 mm
Wire preparation length, output side	8.0...9.0 mm

## Colors & materials

Casing material	Metal
-----------------	-------

## Temperatures & operating conditions

Ambient temperature range	-25...+50 °C
Maximum temperature at tc test point	75 °C
Max.housing temperature in case of fault	110 °C
Temperature range at storage	-40...+85 °C
Permitted rel. humidity during operation	5...85 % <sup>1)</sup>

1) Maximum 56 days/year at 85 %

## Lifespan

<b>ECG lifetime</b>	100000 h / 50000 h <sup>1)</sup>
---------------------	----------------------------------

1) At maximum  $T_c = 65^\circ\text{C}$  / 10% failure rate / At maximum  $T_c = 75^\circ\text{C}$  / 10% failure rate

## Capabilities

<b>Programming interface</b>	Rset
<b>Control interface</b>	DALI
<b>Dimmable</b>	Yes
<b>Dimming interface</b>	DALI-2
<b>Dimming range</b>	10...100 %
<b>Dimming method</b>	Full analogue dimming
<b>DALI-2 Diagnostic Data</b>	No
<b>DALI-2 Energy Data</b>	No
<b>Constant lumen function</b>	Programmable
<b>Max. cable length to lamp/LED module</b>	2.0 m <sup>1)</sup>
<b>Suitable for fixtures with prot. class</b>	I
<b>Suitable for emergency lighting</b>	Yes <sup>2)</sup>
<b>Type of connection, input side</b>	Push terminal
<b>Type of connection, output side</b>	Push terminal
<b>Number of channels</b>	1
<b>Overheating protection</b>	Automatic reversible
<b>Overload protection</b>	Automatic reversible
<b>Short-circuit protection</b>	Automatic reversible
<b>Intended for no-load operation</b>	No
<b>No-load proof</b>	Yes

1) Output wires must be routed as close as possible to each other

2) except those used in high-risk task areas

## Programming

Programming device	DALI magic
Tuner4TRONIC Field App	Yes

## Programmable features

DALI Settings	Yes
DALI-2 Luminaire Data	No
Driver Guard	Yes
Emergency Mode	Yes

## Certificates & standards

Approval marks – approval	CE / ENEC 05 / EL / EAC / CCC / BIS / RCM
Standards	IEC 61347-1 / IEC 61347-2-13 / IEC 62384 / IEC 62386 / IEC 61000-3-2 / IEC 61000-3-3 / IEC 61547
Type of protection	IP20

## Logistical data

Commodity code	85044083900
----------------	-------------

## Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	12-02-2025
Primary Article Identifier	4062172126212
Declaration No. in SCIP database	In work
SCIP_STATUS	In work
SCIP_ID	

### Ecodesign regulation information:

Intended for use with LED modules.

The forward voltage of the LED light source shall be within the defined operating window of the control gear in all operating conditions including dimming if applicable.

Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

## Download Data

File		
Mandatory Publications	PDF	▶ ETI DALI LT2 L CE 4235855 06 200125
Mandatory Publications	PDF	▶ ETI DALI LT2 L UK DoC 4281066 040923
User instruction	PDF	▶ UI ETI DALI LT2 L

## Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172126212 OSRAM	ETi DALI 25/220-240/500 LT2 L	Shipping carton box 20 Pieces	303 x 159 x 105 mm	5.06 dm <sup>3</sup>	176.35 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit

## Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.