




---

 PRODUCT-DETAILS

# OT1250EUUR3AZ

## OT1250EUUR3AZ EMC safety switch




---

**General Information**

Extended Product Type	OT1250EUUR3AZ
Product ID	1SCA103283R1001
EAN	6417019377964
Catalog Description	OT1250EUUR3AZ EMC safety switch

Long Description	<p>EMC safety switch, 3-p. 415V AC23 1250A, 710kW. Mounted auxiliary contact: 2NO1NC. Steel sheet enclosure. IP65. RedYellow Pistol handle. Interlocked cover. Defeatable interlocking. The enclosed switch is using a galvanised steel enclosure, with polyester coating. It is suitable for outdoor use with respect to UV light and ingress protection. The enclosure have inbuilt gas pressure relief function to protect the user in case of an internal arc. The door is earthed via the hinges. The enclosure is prepared for single and parallel cables. Cable entry types can be blank , ring-flange or C-flange type (FL21), with different cable configuration, like top/bottom or bottom/bottom. The handle is padlockable for 3 padlocks, cover is interlocked, and interlock function can be bypassed for thermographing.</p>
------------------	---

---

**Material Compliance**

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
---	-----------------

REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

## Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340016M0005
Mechanical Drawings	OTKM128033PBL8R.stp

## Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363090
Country or Territory of Origin	Finland

## Dimensions

Product Net Width	800 mm
Product Net Height	1200 mm
Product Net Depth / Length	330 mm
Product Net Weight	67.97 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	815 mm
Package Level 1 Depth / Length	1310 mm
Package Level 1 Height	425 mm
Package Level 1 Gross Weight	73 kg
Package Level 1 EAN	6417019377964

## Technical

Cable Entry Position	Bottom/Bottom
Cable Outlets Per Side	Blank / 8xring-flange, Knock-outs: 3x10mm, 12.5mm, 20.5mm, 25.5mm, 32.5mm
Color	RAL7032
Connecting Capacity Main Circuit	Hole Diameter 12 mm Screw Clamp / PE Terminal 10pc,25 ... 120 mm²

Conventional Thermal Current ( $I_{the}$ )	Fully Enclosed 1250 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Steel sheet
Handle Color	Red / Yellow
Handle Type	Pistol handle
Impact Resistance Rating	Housing IK09
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC
Mounted Auxiliary Contacts	2 NO, 1 NC
Neutral Type	No Neutral Terminal
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	2
Number of Poles	3P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 29 W
Rated Insulation Voltage ( $U_i$ )	750 V
Rated Operational Current AC-22A ( $I_e$ )	(380 ... 415 V) 1250 A (500 V) 1250 A (690 V) 1250 A
Rated Operational Current AC-23A ( $I_e$ )	(380 ... 415 V) 1250 A (500 V) 1250 A (690 V) 1250 A
Rated Operational Power AC-23A ( $P_e$ )	(380 ... 415 V) 710 kW (500 V) 900 kW (690 V) 1200 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity ( $I_{cm}$ )	(690 V AC) 110 kA
Rated Short-time Withstand Current Low Voltage ( $I_{cw}$ )	for 1 s 50 kA
Recommended Screw Driver	Main Circuit M12
Special Functions	EMC
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 75 N·m

### Technical UL/CSA

Recommended Screw Driver	Main Circuit M12
Tightening Torque	Main Circuit 75 N·m

### Certificates and Declarations

Declaration of Conformity - CE	1SCC340042D2703
--------------------------------	-----------------

### External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

## Categories

---

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

