

product type designation

Code Reader MV540 S

SIMATIC MV540 S optical reader Resolution: 800 x 600 pixels, Function: 1D/2D code reading; Image field and distance: variable, (ABH lens object); PoE; IP67 with 6GF3540-8AC11; Delivery: Reader and SD card adapter;



suitability for operation

1D codes: Int. 2/5, Code 128, Code 93, Code 39, Code 32, EAN 13, EAN 8, UPC-A, UPC-E, GS1, Pharmacode, Postnet, 2D codes: DMC, dot code, PDF417 (without: Truncated, Micro and Macro), Q R (without: Micro and Macro), verification uncalibrated

interfaces

type of electrical connection

- of Industrial Ethernet interface
- of the RS 422 interface
- of the RS 232 interface
- for supply voltage
- at the digital inputs/outputs

M12, d-coded, PoE

M12, 12-pin, male

M12, 12-pin, male

M12, 12-pin, male

M12, 12-pin, male

number of digital inputs

1

number of digital outputs

3

digital input version

1 fast trigger input

digital output version

1 fast strobe output, 2 potential-free outputs (NPN- PNP-capable)

optical data

design of image sensor / of the camera

CMOS-Chip, 800 x 600

type of image capture

Global shutter with manual or automatic exposure time

range	70 ... 3000 mm
range / note	Using C-mount lenses and lens accessories, the range can be exactly matched to the application
type of light source	Integrated lighting or external lighting according to accessories list
image acquisition frequency / maximum	100 Hz
code reading rate / maximum	80 1/s
type of focusing	Manual adjustment on the lens

supply voltage, current consumption, power loss

supply voltage	
<ul style="list-style-type: none"> • at DC / rated value • at DC 	24 V 19.2 ... 28.8 V
consumed current / at DC / at 24 V	
<ul style="list-style-type: none"> • typical • maximum 	0.2 A 2 A
buffering time / in the event of power failure / minimum	0.01 s

mechanical data

material	Die-cast aluminum
color	petrol blue

ambient conditions

ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport 	50 °C -30 ... +70 °C -30 ... +70 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP67
shock resistance	According to IEC 60068-2
shock acceleration	300 m/s ²
vibrational acceleration	40 m/s ²

design, dimensions and weights

width	68 mm
height	122 mm
depth	45 mm
net weight	0.55 kg
mounting type	4 x M4 screws

product features, product functions, product components / general

protocol / is supported / Media Redundancy Protocol (MRP)	No
product function / of the PROFINET IO device / is supported / H-Sync forwarding	No
protocol / is supported	

- LLDP
- PROFINET IO protocol
- TCP/IP
- SNMP v1
- SNMP v2
- SNMP v3
- DCP
- EtherNet/IP protocol
- OPC UA

Yes
Yes
Yes
Yes
No
No
Yes
No
No

product feature / silicon-free

Yes

standards, specifications, approvals

MTBF

66 y

further information / internet-Links

Internet-Link

- to website: Selector TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://support.industry.siemens.com/cs/ww/en/view/67384964>
<http://www.siemens.com/codereader>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

last modified:

10/05/2020