



EN ISO 20345:2011


 HORIZON
ILLINOIS
 52023-15L

S3 *CI SRC
Size: 36-48
Weight: 700 gr.

Fit: 10,5

Working Environment:
 Multipurpose, Building, Logistics
 and Light Industry, Farming and
 Gardening


FEATURES

UPPER

 Grain leather Hydro 1,8-2,0 mm
 Fabric of High Tenacity

LINING

3D Air circulation 320 gr.

INSOLE

Climaction-Fit 337

TOE CAP

Steel Toe Cap

RESISTANCE TO PERFORATION

Steel Plate

TYPE

Ankle boot

SOLE

PU DUAL-DENSITY SRC

Two-component PU sole with self-cleaning pattern, extremely flexible for various places of use, both indoor and outdoor, with SRC Antislip Standard.

TECHNOLOGIES

Removable Insole

337 climaction fit

Removable anatomic and ergonomic insole. Absorbent and transpiring open-cell foam support. Keeps feet fresh. Specifically-designed thermoforming for exceptional comfort.



Protection elements

STEEL PROTECTION

Steel toecap, with anti-corrosion paint. Protection of over 200J. Comfortable fit. Stainless steel Plate resistant puncture with acid-resistant paint.



Lateral stability

dynamic HC control technology


Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

It supports the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



Electrical features

WED

Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other

DUAL MICRO DWT WICBO

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.



SRC (SRA+SRB)


 SOLE 52 - 53
 PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE °) ≥0.28	0.36 0.42
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE °) ≥0.13	0.19 0.14

EN ISO 20344:2011