


Geberit Mapress Stainless Steel T-piece with female thread (FKM, blue)



Example image



APPLICATION PURPOSES

- For chemicals and technical liquids
- For district heating water ≤ 140 °C
- For thermal media (solar)
- For mineral and lubricating oil
- For motor fuels (e.g. diesel)

- For compressed air (oil purity class 0–4)
- For solar technology, industry and shipbuilding
- For industrial gases (e.g. acetylene, shielding gases)

- Silicone-free (LABS-free)
- Seal ring made of FKM, blue
- Pressing socket with black protection plug

CHARACTERISTICS

- Pressing indicator

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
50413	12 / 15 / 12	15	1/2	15	90	6.4	4	3.2	3.2	1.2	2.7	1.2
50414	15	18	1/2	18	90	6.8	4.2	3.4	3.4	1.4	2.9	1.4
50415	15 / 20 / 15	18	3/4	18	90	6.8	4.4	3.4	3.4	1.4	2.9	1.4
50416	20 / 15 / 20	22	1/2	22	90	7.4	4.3	3.7	3.7	1.6	3	1.6
50417	20	22	3/4	22	90	7.4	4.6	3.7	3.7	1.6	3.1	1.6

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
50418	25 / 15 / 25	28	1/2	28	90	8.4	4.6	4.2	4.2	1.9	3.3	1.9
50419	25 / 20 / 25	28	3/4	28	90	8.4	4.9	4.2	4.2	1.9	3.4	1.9
50420	25	28	1	28	90	8.4	5.3	4.2	4.2	1.9	3.6	1.9
50421	32 / 15 / 32	35	1/2	35	90	10	5	5	5	2.4	3.7	2.4
50422	32 / 20 / 32	35	3/4	35	90	10	5.3	5	5	2.4	3.8	2.4
50424	40 / 15 / 40	42	1/2	42	90	11.4	5.3	5.7	5.7	2.7	4	2.7
50425	40 / 20 / 40	42	3/4	42	90	11.4	5.6	5.7	5.7	2.7	4.1	2.7
50427	50 / 15 / 50	54	1/2	54	90	13.8	5.9	6.9	6.9	3.4	4.6	3.4
50428	50 / 20 / 50	54	3/4	54	90	13.8	6.2	6.9	6.9	3.4	4.7	3.4
50429	50	54	2	54	90	13.8	7.9	6.9	6.9	3.4	5.6	3.4
50437	65 / 20 / 65	76.1	3/4	76.1	90	23	7.4	11.5	11.5	6.2	5.9	6.2
50438	65 / 50 / 65	76.1	2	76.1	90	23	9.1	11.5	11.5	6.2	6.8	6.2
50440	80 / 20 / 80	88.9	3/4	88.9	90	26	8	13	13	7	6.5	7

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
50441	80 / 50 / 80	88.9	2	88.9	90	26	9.7	13	13	7	7.4	7
50443	100 / 20 / 100	108	3/4	108	90	31	9	15.5	15.5	8	7.5	8
50444	100 / 50 / 100	108	2	108	90	31	10.7	15.5	15.5	8	8.4	8