

GRM-KIT-C0G-DE

No	Murata P/N	Size (mm/inch)	TC Code	Rated Vo	Cap.	Tol.	Thickness	Qty
1	GRM1885C1H101JA01	1608M/0603	C0G	50Vdc	100pF	±5%	0.9max	100
2	GRM1885C1H151JA01	1608M/0603	C0G	50Vdc	150pF	±5%	0.9max	20
3	GRM1885C1H221JA01	1608M/0603	C0G	50Vdc	220pF	±5%	0.9max	20
4	GRM1885C1H331JA01	1608M/0603	C0G	50Vdc	330pF	±5%	0.9max	20
5	GRM1885C1H471JA01	1608M/0603	C0G	50Vdc	470pF	±5%	0.9max	20
6	GRM1885C1H681JA01	1608M/0603	C0G	50Vdc	680pF	±5%	0.9max	20
7	GRM1885C1H102JA01	1608M/0603	C0G	50Vdc	1000pF	±5%	0.9max	100
8	GRM1885C1H152JA01	1608M/0603	C0G	50Vdc	1500pF	±5%	0.9max	20
9	GRM1885C1H222JA01	1608M/0603	C0G	50Vdc	2200pF	±5%	0.9max	20
10	GRM1885C1H332JA01	1608M/0603	C0G	50Vdc	3300pF	±5%	0.9max	20
11	GRM1885C1H472JA01	1608M/0603	C0G	50Vdc	4700pF	±5%	0.9max	20
12	GRM1885C1H682JA01	1608M/0603	C0G	50Vdc	6800pF	±5%	0.9max	20
13	GRM1885C1H103JA01	1608M/0603	C0G	50Vdc	0.01μF	±5%	0.9max	100
14	GRM2165C2A101JA01	2012M/0805	C0G	100Vdc	100pF	±5%	0.7max	100
15	GRM2165C2A151JA01	2012M/0805	C0G	100Vdc	150pF	±5%	0.7max	20
16	GRM2165C2A221JA01	2012M/0805	C0G	100Vdc	220pF	±5%	0.7max	20
17	GRM2165C2A331JA01	2012M/0805	C0G	100Vdc	330pF	±5%	0.7max	20
18	GRM2165C2A471JA01	2012M/0805	C0G	100Vdc	470pF	±5%	0.7max	20
19	GRM2165C2A681JA01	2012M/0805	C0G	100Vdc	680pF	±5%	0.7max	20
20	GRM2165C2A102JA01	2012M/0805	C0G	100Vdc	1000pF	±5%	0.7max	100
21	GRM2165C2A152JA01	2012M/0805	C0G	100Vdc	1500pF	±5%	0.7max	20
22	GRM2165C2A222JA01	2012M/0805	C0G	100Vdc	2200pF	±5%	0.7max	20
23	GRM2165C2A332JA01	2012M/0805	C0G	100Vdc	3300pF	±5%	0.7max	20
24	GRM2165C1H472JA01	2012M/0805	C0G	50Vdc	4700pF	±5%	0.7max	20
25	GRM2195C1H682JA01	2012M/0805	C0G	50Vdc	6800pF	±5%	0.95max	20
26	GRM2195C1H103JA01	2012M/0805	C0G	50Vdc	0.01μF	±5%	0.95max	100
27	GRM2195C1H153JA01	2012M/0805	C0G	50Vdc	0.015μF	±5%	0.95max	20
28	GRM21B5C1H223JA01	2012M/0805	C0G	50Vdc	0.022μF	±5%	1.35max	20
29	GRM3195C2A222JA01	3216M/1206	C0G	100Vdc	2200pF	±5%	0.95max	20
30	GRM3195C2A332JA01	3216M/1206	C0G	100Vdc	3300pF	±5%	0.95max	20
31	GRM3195C2A472JA01	3216M/1206	C0G	100Vdc	4700pF	±5%	0.95max	20
32	GRM3195C2A682JA01	3216M/1206	C0G	100Vdc	6800pF	±5%	0.95max	20
33	GRM3195C2A103JA01	3216M/1206	C0G	100Vdc	0.01μF	±5%	0.95max	100
34	GRM3195C2A153JA01	3216M/1206	C0G	100Vdc	0.015μF	±5%	0.95max	20
35	GRM3195C2A223JA01	3216M/1206	C0G	100Vdc	0.022μF	±5%	0.95max	20
36	GRM31M5C2A473GA01	3216M/1206	C0G	100Vdc	0.047μF	±2%	1.25max	20
37	GRM31C5C1H683JA01	3216M/1206	C0G	50Vdc	0.068μF	±5%	1.8max	20
38	GRM31C5C2A104JA01	3216M/1206	C0G	100Vdc	0.1μF	±5%	1.8max	100
39	GRM31C5C1E124JA01	3216M/1206	C0G	25Vdc	0.12μF	±5%	1.8max	20