



Example image

APPLICATION PURPOSES

- For compressed air (oil purity class 0–X)
- For district heating water ≤ 140 °C
- For motor fuels (e.g. diesel)
- For mineral and lubricating oil

CHARACTERISTICS

- Pressing socket with black protection plug

- Spindle caulk made of PTFE
- Section seal of flange and ball made of PTFE
- Fulfils requirements in accordance with TA Air VDI 2440
- Connecting flange for motor in accordance with EN ISO 5211 (only for d = 76.1–108 mm)
- Length-adjustable actuator lever (only for d = 108 mm)
- Pressing indicator
- Leaky if unpressed
- Seal ring made of FKM, blue

TECHNICAL DATA

Operating temperature	-25 – +180 °C
Product material	CrNiMo steel 1.4401 (EN 10088)

TO ORDER ADDITIONALLY

- Actuator lever set, lockable, for Geberit Mapress ball valve, flanged

Art. no.	DN	DNV	d, ø mm	k mm	m mm	L cm	L1 cm	L2 cm	Z cm	PN bar
50780	12	15	15			12.2	5	9.3	4.1	16
50782	20	20	22			13.3	5.6	10.3	4.5	16
50783	25	25	28			14.2	6.6	12.8	4.8	16
50784	32	32	35			17	7.5	12.8	5.9	16

<i>Art. no.</i>	<i>DN</i>	<i>DNV</i>	<i>d_ø</i> <i>mm</i>	<i>k</i> <i>mm</i>	<i>m</i> <i>mm</i>	<i>L</i> <i>cm</i>	<i>L1</i> <i>cm</i>	<i>L2</i> <i>cm</i>	<i>Z</i> <i>cm</i>	<i>PN</i> <i>bar</i>
50785	40	40	42			19.4	8.5	15.8	6.7	16
50786	50	50	54			22.1	9.6	15.8	7.5	16
50787	65	65	76.1	70	9	29.1	13.5	22.3	9.2	16
50788	80	80	88.9	70	9	33.3	14.5	35.8	10.6	16
50789	100	100	108	102	11	41.2	17.7	50	13.1	16