

CODE: ESP3604

NARDI Esprit 3T 60/4
Oil-Free Air Compressor



Tubular 3 Litre
frame air receiver

Brushless
induction
motor

4x anti-vibration
feet

Flat twin-cylinder
direct-drive
oil-free pump

3 YEAR
WARRANTY



MADE IN
ITALY



CODE: ESP3604

NARDI Esprit 3T 60/4

Oil-Free Air Compressor

Flat Twin Esprit Pump: Oil Free Direct Driven Pump Unit

Brushless Induction Motor: 4 Pole, Slow Running for Longer Life

Air Pressure Regulator & Pressure Cut-off switch

Convenient Tubular Frame Air Receiver

Fan Cooled: Extended Running Times

Oil Free Pump: Enhanced Reliability

Four Anti-Vibration feet

Low Noise: High Efficiency

Lightweight & Portable

Compact Design with Easy Carry Handle



Code:	ESP3604
Input Supply	230 V (13 A)
Motor	0.75hp (0.5kw), 4-pole (1400rpm)
Air Receiver (tubular)	3 Litres
Piston Disp.	3.7 CFM
F.A.D.	2.59 CFM
Max. Air Pressure	10 bar (145 psi)
Noise Level	52 dB(A)
Net Weight	13.5kg
Pack Dimensions	450 x 310 x 330mm

Contents

NARDI Esprit 3T 60/4 compressor

Instruction manual