



**ENGINEERED IN
GERMANY**



Product number 1153340118
EAN 4007123174119

DESCRIPTION

- Extremely sturdily constructed extension lead made from highly break-resistant polycarbonate.
- Special feature: cable output is fitted opposite the switch for easy use, e.g. when placed under a desk.
- Rubber pads prevent extension lead from slipping.
- Earthed sockets in a 45° arrangement, ideal for angular plugs.
- The distance between the sockets allows the use of large charger units.
- Optimal mounting option with screw holes for easy fixed mounting of the extension lead, e.g. on the wall.
- With practical hanging facility.
- Illuminated 2-pole ON/OFF safety switch.
- 16 A fuse.
- Sockets with increased touch protection.

TECHNICAL DATA

Cable quality	PVC	Max. current carrying capacity	16 A
Cable length	2.5 m	USB charging units	/Technische Attribute/Anschlussbuchse/nicht zutreffend
Cable designation	H05VV-F 3G1,5	With surge protection	No
Plug system plug	Type E and F (Protective contact with earth hole)	With interference suppressor filter	No
Socket outlets total	8	Colour	silver
Circuit breaker	No		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.96 kg
Weight of product (without packaging)	0.94 kg	Dimension LxWxH (incl. packing)	6 cm x 10 cm x 65 cm
Dimension LxWxH (without packing)	6 cm x 10 cm x 65 cm		