



Main

Range	Easy TeSys
Range of product	Easy TeSys Protect
Product or component type	Differential thermal overload relay
Device short name	LRN
Relay application	Motor protection
Phase failure sensitivity	Tripping current I 30 % of I _r on one phase, the others at I _r conforming to IEC 60947-4-1

Complementary

Product compatibility	LC1N40...95
Range compatibility	EasyPact EasyPact D3N LC1N
Network type	AC
Network frequency	50...60 Hz
Mounting support	Under contactor Plate, with specific accessories Rail, with specific accessories
Thermal overload class	Class 10A conforming to IEC 60947-4-1
Signalling function	Relay trip indicator
Thermal protection adjustment range	17...25 A
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
Mechanical robustness	Shocks: 6 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 3 GN conforming to IEC 60068-2-6
Auxiliary contact composition	1 NO + 1 NC
[I _{th}] conventional free air thermal current	5 A for signalling circuit
[U _e] rated operational voltage	<= 690 V AC
Associated fuse rating	50 A gG for power circuit 25 A aM for power circuit 5 A gG for signalling circuit
[U _i] rated insulation voltage	690 V conforming to IEC 60947-4-1
[U _{imp}] rated impulse withstand voltage	6 kV
Local signalling	Trip indicator
Control type	Push-button red stop: Push-button green reset:
Temperature compensation	-20...60 °C
Connections - terminals	Signalling circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible without cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 4...35 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 4...35 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 4...35 mm ² - cable stiffness: solid without cable end
Recommended tightening torque	9 N.m - on screw clamp terminals

Height	54 mm
Width	70 mm
Depth	113 mm
Net weight	0.51 kg

Environment

Standards	IEC 60947-4-1 GB 14048
Product certifications	CCC
Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...60 °C without derating conforming to IEC 60947-4-1 -20...70 °C with derating
Ambient air temperature for storage	-60...80 °C
Fire resistance	850 °C conforming to IEC 60068-2-1
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Electromagnetic compatibility	Surge withstand: 6 kV conforming to IEC 60801-5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.7 cm
Package 1 Width	8.7 cm
Package 1 Length	12.3 cm
Package 1 Weight	494 g
Unit Type of Package 2	S02
Number of Units in Package 2	9
Package 2 Height	15 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	4.84 kg
Unit Type of Package 3	P06
Number of Units in Package 3	144
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	87.44 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins