

Lamp Current (A): 1.0A
 Ignitor Voltage (Min.): 1.8KV
 Luminaire Rating: Open/Enclosed
 Burning Position: Universal

HPSE 70W/E27/HO
Product Number: 00400
Lamp Type: HIGH PRESSURE SODIUM



Performance Data

Light Output (Lumens @ 100 hours)	6000
Lamp Lumens Per Watt	86
Rated Life (Hrs. @ 10 Hr. /Start)	28000+
Correlated Colour Temperature (K)	2000
Chromaticity (CIE - X Y)	540, 420
Colour Rendering Index (CRI) or (Ra)	20
Typical Warm Up Time (Minutes)	5
Typical Hot Restart Time (Minutes)	1
Burning Position	Universal



Physical Data / Requirements

Base Designation	E27
Bulb Designation	E70
Bulb Diameter (mm)	72
Max. Overall Length (mm)	156
Light Centre Length (mm)	-
Effective Arc Length (mm)	-
Max. Base Temperature (°C)	210
Max. Bulb Temperature (°C)	400
Luminaire Type	Open/Enclosed
Socket Pulse Rating (KV)	2.8
Mercury Content (mg)	3.75

Lumen Maintenance

Lamp Mortality


Lamp Electrical Data / Requirements

IEC Standard	-
Lamp Wattage (W)	70
Lamp Operating Voltage (V)	90
Lamp Operating Current (Amps)	1.0
Min. Open Circuit Voltage (RMS)	198
Min. Starting Pulse (Peak V)	1800-2300
Min. Pulse Width at V (microseconds)	1
Min. Pulse Rate Per 1/2 cycle	1
Pulse Position (Electrical Degrees)	60-90, 240-270

Revision: 20120-10-2

Notes:

1) This Product Specification contains data about typical performance at nominal power. Actual values may depend on ballast and applications. Complies with (CE), Low Voltage (CE), WEEE and RoHS Directives.