

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® KR-M ATEX plus	29.11.2013

For the benefits, refer to SKINTOP® K-M ATEX plus



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEX IBE 13.0027X
Colour delivered:	RAL 9005 black/UV-resistant
Material:	Body: special polyamide Seal: special elastomer O-ring: CR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-20°C to +80°C

Product Management	Document: LAPP_PRO982EN.pdf	1 / 2
--------------------	-----------------------------	-------



SKINTOP® KR-M ATEX plus

29.11.2013

Part number	Article designation / size	Clamping range ØF (mm)	Thread M	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)
SKINTOP® KR-M ATEX plus						
54115205	KR-M 12 ATEX plus	2-4	12 x 1.5	15	26,5 - 30	8.0
54115215	KR-M 16 ATEX plus	4-6	16 x 1.5	19	29 - 34	8.0
54115225	KR-M 20 ATEX plus	5-10	20 x 1.5	25	34 - 37	9.0
54115235	KR-M 25 ATEX plus	6-13	25 x 1.5	30	35 - 40	10.0
54115245	KR-M 32 ATEX plus	9-15	32 x 1.5	36	39 - 47	10.0
54115255	KR-M 40 ATEX plus	16-23	40 x 1.5	46	43 - 52	10.0
54115265	KR-M 50 ATEX plus	22-29	50 x 1.5	55	54 - 62	12.0
54115275	KR-M 63 ATEX plus	29-39	63 x 1.5	66	59 - 71	12.0