

LEDBHR25W

25W – 2000lm LED Energy Saver Bulkhead Light

Features & Benefits

- Round LED Bulkhead Light
- A powerful and energy saving alternative to standard bulkhead lights
- Wide light diffusion pattern
- Robust die cast housing with tough polycarbonate lens suitable for industrial, commercial and home installations
- IP65 weatherproof rating



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
Earth Class Rating	Class I
Operating Temperature	-10°C to +40°C
Ingress Protection Rating	IP65
Wattage	25
Beam Angle	120°
Energy Efficiency	Class G
Energy Usage	26.5KwH/1000H
Lumen output (lm)	2000

Data sheet

LEDBHR25W

Light / LED Lighting

Colour Temperature (K)	5000
LED Type	SMD (On LED Plate)
Mounting Hole Centres (mm)	155
Multiple Unit Support	Yes
Cable Entry(s)	Back Entry, Side Entry (Lip In Housing)

General

Weight (g)	835
Height (mm)	244
Width (mm)	244
Depth (mm)	75
Body Construction	Polycarbonate (Front Cover), Aluminium (Body)
Product Colour	Silver
Accessories (Included)	Fittings
EAN Number	5012483012659
Guarantee Period	3 Years

Data sheet

LEDBHR25W

Light / LED Lighting

Line Diagrams

