


Technical data

RNA0-16X24X13

Needle roller bearing, machined-ring, separable, without inner ring

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
Fw - Under rollers diameter	16 mm
D - External diameter	24 mm
C - Width of bearing, drawn cup or outer ring	13 mm
E - Upper roller diameter	20 mm
rs - Min fillet radius	0,3 mm
Lubrication hole on outer ring	Non/No
Radial clearance class	CN
Precision class	P0



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

RNA0-16X24X13

Needle roller bearing, machined-ring, separable, without inner ring

PRODUCT DEFINITION

Mass	0,021 kg
------	----------

PRODUCT PERFORMANCE

Cr - Dynamic load rating	9050000 mN
C0r - Static load rating	11800000 mN
N lim - Grease lubrication limit speed	90000 °/s
N lim - Oil lubrication limit speed	138000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

db - Shoulder diameter IR	19,6 mm
Da max - Max shoulder diameter OR	22 mm
Db - OR smooth shaft shoulder diameter	16,4 mm
ras max - Max shaft & housing fillet radius	0,3 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15