


## FEATURES

- **Fluoroelastomer material:** Provides superior chemical resistance and longevity
- **Shore A hardness 90 to 95:** Ensures optimal flexibility and sealing performance
- **Wide temperature range:** Operates efficiently from -20 °C to 140 °C
- **Precision dimensions:** Inside diameter of 126.72 mm and outside diameter of 130.28 mm for accurate fitting
- **Compliance with standards:** Meets BS ISO 3601-1, AS 568, and other key standards for quality assurance

## RS PRO 126.72 mm O-Ring Seal, Black Fluoroelastomer

RS Stock No: 732-023



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in demanding environments. Made from high-quality fluoroelastomer materials, it offers excellent chemical resistance and durability. Ideal for applications requiring a robust seal, it operates effectively within a temperature range of -20 °C to 140 °C.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	126.72 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	130.28 mm
Thickness	1.78 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

