




Professionally approved products.

Product Datasheet

PTFE Insulated Equipment Wire (Type A)

19/0.15mm SPC



RoHS✓



Characteristics:

Relevant Standards: BS 3G 210:1996

Rated Voltage: 300 Vrms

Working Temperature (°C): -75 to 200 °C

Construction:

Inner Conductor: Silver plated copper

Insulation: PTFE

Specification:

Conductor				Insulation Thickness (mm)		Overall Diameter (mm)		Conductor resistance (Ω/Km, at 20°C)	Mass	Long term current Rating (A)
Size AWG	Area (mm ²)	O/D (mm)	Stranding (mm)	Min.	Max.	Min.	Max.	SPCW Max.	Max (Kg/Km)	Max.
22	0.336	0.750	19/0.15	0.10	0.15	0.95	1.10	58.6	4.41	8.0

*Current ratings are based on a temperature rise of 40°C (single wire in free air)

Product Range:

RS Code	Description
8055825	PTFE A 19/0.15 black 100m
8055831	PTFE A 19/0.15 white 100m
8055834	PTFE A 19/0.15 pink 100m
8055837	PTFE A 19/0.15 red 100m
8055840	PTFE A 19/0.15 yellow 100m
8055843	PTFE A 19/0.15 blue 100m
8055847	PTFE A 19/0.15 orange 100m
8055853	PTFE A 19/0.15 violet 100m
8055856	PTFE A 19/0.15 green 100m
8055859	PTFE A 19/0.15 brown 100m
8055862	PTFE A 19/0.15 grey 100m