

Main

| | |
|------------------------------------|---|
| Range | Resi9 |
| Product or component type | Vertical comb busbar |
| Mounting mode | Vertical |
| Accessory / separate part category | Connection accessory |
| Poles description | 3P + N |
| Number of ways | 1 way for top N + 3 L with 18 mm pitch 1 way for bottom N + 3 L with 18 mm pitch |
| Height pitch dimension | 150 mm |
| Connection pitch | 18 mm top - 18 mm bottom |
| Total number of 18 mm modules | 2 |





Complementary

| | |
|--------------------------------|---|
| Incomer device | Resi9 XP ID |
| [In] rated current | 63 A |
| [Ue] rated operational voltage | 230 V AC 50 Hz Ph/N 400 V AC 50 Hz Ph/Ph |
| [Ui] rated insulation voltage | 250 V AC 50 Hz |
| Standards | EN/IEC 61439-1 |
| Product certifications | CE |
| 9 mm pitches | 4 |
| Width | 36.5 mm |
| Depth | 21 mm |
| Colour | White (RAL 9003) |
| Range compatibility | Resi9 Resi9 XP ID |

Environment

| | |
|-----------------|---|
| Fire resistance | 850 °C (30 s) conforming to IEC 60695-2-1 |
|-----------------|---|

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |