



Push Splice Push Grip

TE Internal #: 2324697-2

Closed End Splice, 22 – 12 AWG, .5 – 2.5 mm² Wire, 2 Splice Capacity, Standard, Yellow - Translucent, Bag/Box, Closed Barrel, Push Splice Push Grip

[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: Closed End Splice

Wire Size: .5 – 2.5 mm²

Sealable: No

Splice Capacity: 2

Features

Product Type Features

Splice Type	Closed End Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Splice Capacity	2
Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Operating Voltage	600 VAC
Current Rating	24 A

Body Features

Splice Features	Standard
Primary Product Color	Yellow - Translucent

Contact Features

--	--



Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	.5 – 2.5 mm²
-----------	--------------

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	IEC, UL
Compatible With Approved Standards Products	IEC 60988-2-2, UL 486C
Government Qualified Splice	No

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1-2213678-3 Z35 MINI LED HOLDER 12*15MM PH, NO TAPE</p>	 <p>TE Part # CR2100-000 CPGI-WC-TG-TN-BULK</p>	 <p>TE Part # 2-2154857-3 Socket, SCALABLE LED, 2PC, Gold, w /TS</p>	 <p>TE Part # 1811027-1 ASSEMBLY,12AWG TAP</p>
 <p>TE Part # 2213118-2 LUMAWISE LED HOLDER Z32 LOW PROFILE 1215</p>	 <p>TE Part # 2154857-3 HOLDER, SCALABLE LED, 2PC</p>	 <p>TE Part # 2325811-3 LUMAWISE Z45 LED HOLDER 20X24</p>	 <p>TE Part # 2388553-2 PUSH-IN CONNECTOR, 2 POS</p>
 <p>TE Part # 2213480-2 LUMAWISE Z50 LED HOLDER 2727 GENERAL</p>	 <p>TE Part # 6-2154874-1 Scalable LED Holder 13.5x13.5 (1pc)</p>	 <p>TE Part # CR2108-000 CPGI-WC-WNG-YW-BULK</p>	 <p>TE Part # CR2105-000 CPGI-WC-WG-YW-BULK</p>
 <p>TE Part # 2-2213678-6 Z35 13.5*13.5MM PANHEAD OSRAM PACKAGING</p>	 <p>TE Part # CR2091-000 CPGI-WC-CG-RD-BULK</p>	 <p>TE Part # 6-2154874-2 Scalable LED Holder 19x19 (1pc)</p>	 <p>TE Part # CR2107-000 CPGI-WC-WNG-RD-BULK</p>







TE Part # CR2092-000
CPGI-WC-CG-YW-BULK





TE Part # CR2099-000
CPGI-WC-TG-GR-BULK





TE Part # 1-2325811-3
LUMAWISE Z45 LED HOLDER 20X24





TE Part # 2-2154857-1
Socket, SCALABLE LED, 2PC, Gold, w /TS

Also in the Series | Push Splice Push Grip




Splices(5)

Customers Also Bought






TE Part #1-2325807-2
LUMAWISE Z45 LED HOLDER 19X19





TE Part #171505-2
PIDG RING UL.CSA(22-18)



TE Part #211883-5
SCREW RETAINER KIT,AMPLIMITE





TE Part #2834048-1
PLUG, 2P LATCHED POKE-IN WTW CONN.NL



TE Part #C67976-000
B-155-9001





TE Part #181902-1
250 FASTON,REC.,24-17 AWG,TPBR



TE Part #5745136-3
SCREW RETAINER KIT





TE Part #1-2834049-1
REC MOD, 2P LATCHED POKE-IN WTW CONN.NL





TE Part #321890
TERMINAL,SOLIS R HT 22-16 8





TE Part #34105
SOLIS R 22-16 COMM 22-18 MIL 6



Documents

Product Drawings

PUSH GRIP CONNECTOR 2P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2324697-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2324697-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2324697-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

COMPACT PUSH GRIP WIRE CONNECTORS

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

FIMKO Certificate

English