

Jigsaw XGT®

JV001G

40Vmax, 800 - 3 500 min⁻¹

Model JV001G is a cordless jig saw powered by 40Vmax XGT® Li-Ion battery

This model is more efficient than our existing AC and DC models, allowing for smooth and efficient cutting of 48mm thick MDF. Higher user-friendliness has been achieved by adding light reduction function, redesigning tool body shape and more



XGT **BL** **SOFT**
MOTOR NO LOAD

Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	800 - 3500 min ⁻¹
Length of Stroke	26 mm
Max. Bevel Range (Left)	0 - 45 °
Max. Bevel Range (Right)	0 - 45 °
Capacity Aluminium	20 mm
Max. Cutting Capacity in Wood (90°)	135 mm
Max. Cutting Capacity in Steel (90°)	10 mm
Orbital Action	✓
Electronic brake	✓
Sound Power Level (L _{WA})	98 dB(A)
Vibration Level, Cutting Sheet Metal	4,8 m/s ²
Sound Pressure Level (L _{pA})	90 dB(A)

User benefits

- Variable speed control dial enables user to match the speed to the application for greater versatility
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating
- 3 orbital settings

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing