

Product data sheet

Specifications



Repacked, bell transformer, Acti9 iTR, 230VAC, 16VA, 8V to 12V output

A9A15212W



This repacked option saves 7.686 over the standard condition

Main

range of product	Acti9
Product name	Acti9 iTR
Product or component type	Transformer
Device short name	iTR
Transformer type	Bell transformer

Complementary

[Ue] rated operational voltage	230 V AC 50 Hz
Output voltage	8/12 V: +/- 15 % on load 13/18 V: off load
Output short-circuit protection	Built-in
rated power in VA	16 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	4
Height	89 mm
Width	36 mm
Depth	60 mm
Colour	White
Auxiliary connection terminal	Tunnel type terminalsrigid 2.5 mm ² Tunnel type terminalsflexible 2.5 mm ² Tunnel type terminalsflexible with ferrule 2.5 mm ²
Wire stripping length	5 mm
Tightening torque	0.5 N.m

Environment

Standards	IEC 61558-2-6 EN 61558-2-6 EN 60742
Product certifications	NF
IP degree of protection	IP20 conforming to IEC 60529
Overvoltage category	Class II with terminal shields in option
Ambient air temperature for operation	-20...55 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient air temperature for storage	-25...80 °C
-------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	8.500 cm
Package 1 Length	13.000 cm
Package 1 Weight	384.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.025 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

8 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

6edbd8bf-8086-4f8e-a012-80f9e4a1db80

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins