

Rear panel, PrismaSeT P, for enclosure W 650mm, IP31

LVS08736

EAN Code: 3606481877772

Main

Range	PrismaSeT	
Range of product	PrismaSeT P	
Product or component type	Rear panel	
Range compatibility	PrismaSeT PrismaSeT P enclosure	
Device application	Low voltage electrical distribution	
Enclosure type	Metal enclosure	
installation description	Cubicle - width 650 mm	
Kit composition	side panel	
Standards	IEC 61439-1 for enclosure IEC 61439-2 for enclosure	
Product certifications	ASTA	

Complementary

Material	Treated sheet steel	
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Surface finish	Matt Textured	
Colour	White (RAL 9003)	
Special colour options	Yes	
Width	650 mm	
Height	2000 mm	
Net weight	12.02 kg	
Quantity per set	Set of 1	

Environment

IP degree of protection	IP30 for enclosure
IK degree of protection	IK08

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	68.500 cm

Package 1 Length	105.500 cm
Package 1 Weight	12.306 kg
Unit Type of Package 2	P12
Number of Units in Package 2	15
Package 2 Height	74.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	196.590 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



- All dimensions are approximate and are in $\boldsymbol{\pi}$ Also see technical documentation.