



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Contact Insert**

Contact Type: **Socket**

Pole Configuration: **16+PE**

## Features

### Product Type Features

Rectangular Connector Insert Type	Contact Insert
-----------------------------------	----------------

### Electrical Characteristics

Power Circuit Voltage	400 V
-----------------------	-------

### Body Features

Primary Product Color	Gray
-----------------------	------

### Contact Features

Contact Type	Socket
--------------	--------

Pole Configuration	16+PE
--------------------	-------

### Packaging Features

Packaging Method	Box
------------------	-----

Packaging Quantity	5
--------------------	---

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
------------------------------	------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold:
--	---

Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | **HDC HSB**



Insertion & Extraction Tools(2)



Rectangular Contact Inserts(8)

Customers Also Bought



TE Part #ZPF00000000203399  
DMC-MR 30-23 PD



TE Part #ZPF00000000202098  
732-8052-18 WA



TE Part #CZ6862-000  
HEX40-AC-45-25-A12-3



TE Part #ZPF00000000202094  
DMC-M 0402 AW 01



TE Part #ZPF000000000203398  
DMC-MR 30-23 PC



TE Part #ZPF000000000201129  
732-8052-31 WA



TE Part #ZPF000000000203708  
DMC-M 99-10 PC



TE Part #225398-6  
CONNECTOR, BNC DUAL CRIMP  
JACK

## Documents

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_7-1103639-9\\_D.2d\\_dxf.zip](#)

English

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_7-1103639-9\\_D.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_7-1103639-9\\_D.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.