

C16BH3FM

Circuit breaker frame, ComPacT NS1600bH, 70kA at 415VAC, 1600A, 3P, fixed, manually operated, without control unit

Main

Range	ComPacT
Range of product	ComPacT NS1600b...3200 new generation
Product or component type	Basic frame
Device application	Distribution
Number of poles	3P
[In] rated current	1600 A at 50 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category B
[Icu] rated ultimate short-circuit breaking capacity	125 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	H 70 kA 415 V AC
Control type	Manually operated
Mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	94 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 64 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 64 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] rated short-time withstand current	32 kA 3 s conforming to IEC 60947-2
Integral instant protection	130 kA
Mechanical durability	5000 cycles conforming to IEC 60947-2
Electrical durability	1000 Cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 2000 Cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 2000 Cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 3000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Power losses	84 W
Mounting support	Backplate
Connection pitch	70 mm
Protection type	Without protection
Height (H)	350 mm
Width (W)	420 mm
Depth (D)	160 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 60947-2
Product certifications	IECEE CB Scheme
Pollution degree	3 conforming to IEC 60947
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins