


19

SOCKET 1/2" hexagon UD profile

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- * not standardised

12.5

1/2"



mm

Code	No.	12.5	*	O mm	L	d ₁	d ₂	t	1/2"	£
6130020	198			8	38.0	13.0	22.5	15.0	55	10
6130100	199		*	9	38.0	14.2	22.5	15.0	56	10
6130290	1910			10	38.0	15.5	22.5	13.5	56	10
6130370	1911			11	38.0	16.7	22.5	12.5	58	10
6130450	1912			12	38.0	18.0	22.5	12.5	58	10
6130530	1913			13	38.0	19.2	22.5	12.5	61	10

Code	No.	12.5	*	O mm	L	d ₁	d ₂	t	1/2"	£
6130610	1914			14	38.0	20.5	22.5	12.5	63	10
6130880	1915			15	39.5	21.7	23.8	15.0	74	10
6130960	1916			16	39.5	22.5	23.8	15.0	75	10
6131180	1917			17	39.5	24.0	22.5	15.0	74	10
6131260	1918			18	39.5	25.5	23.0	17.0	73	10
6131340	1919			19	40.0	26.7	24.2	17.0	85	10
6131420	1920			20	40.0	28.0	25.5	17.0	96	10
6131500	1921			21	41.5	29.2	26.0	18.5	106	10
6131690	1922			22	41.5	30.5	26.3	18.5	112	10
6131770	1923		*	23	41.5	31.7	27.5	18.5	122	10
6131850	1924			24	41.5	33.0	28.0	18.5	132	10
6131930	1925		*	25	41.5	34.2	28.8	18.5	139	10
6132070	1926		*	26	41.5	35.5	29.4	18.5	148	10
6132150	1927			27	41.5	36.7	30.0	18.5	157	10
6132230	1928		*	28	43.0	38.0	30.5	20.0	168	10
6132310	1929		*	29	43.0	39.2	31.2	20.0	181	10
6132580	1930			30	43.0	40.5	32.5	20.5	193	10
6132740	1932			32	44.5	43.0	34.5	22.5	226	10
2545306	1933		*	33	44.5	44.2	36.0	22.5	226	10
6138270	1934			34	44.5	45.5	37.0	22.5	259	10
1718711	1936		*	36	44.5	48.0	38.0	22.5	271	10

D 19

SOCKET 1/2" bi-hexagon UD profile


- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- GEDORE vanadium steel 31CrV3, polished, chrome-plated
- * not standardised

12.5

1/2"



AF



mm

Code	No.	12.5	*	O mm	L	d ₁	d ₂	t	1/2"	£
6133040	D 198			8	38.0	13.0	22.5	7.0	51	10
6133120	D 199		*	9	38.0	14.2	22.5	8.0	52	10
6133200	D 1910			10	38.0	15.5	22.5	13.5	56	10
6133390	D 1911			11	38.0	16.7	22.5	12.5	57	10
6133470	D 1912			12	38.0	18.0	22.5	12.5	57	10
6133550	D 1913			13	38.0	19.2	22.5	12.5	59	10
6133630	D 1914			14	38.0	20.5	22.5	12.5	61	10
6133710	D 1915			15	39.5	21.7	23.8	15.0	72	10
6133980	D 1916			16	39.5	22.5	23.8	15.0	72	10
6134010	D 1917			17	39.5	24.0	22.5	15.0	70	10
6134280	D 1918			18	39.5	25.5	23.0	17.0	68	10
6134360	D 1919			19	40.0	26.7	24.2	17.0	81	10
6134440	D 1920			20	40.0	28.0	25.5	17.0	90	10
6134520	D 1921			21	41.5	29.2	26.0	18.5	101	10
6134600	D 1922			22	41.5	30.5	26.3	18.5	106	10
6134790	D 1923		*	23	41.5	31.7	27.5	18.5	118	10
6134870	D 1924			24	41.5	33.0	28.0	18.5	123	10
6134950	D 1925		*	25	41.5	34.2	28.8	18.5	131	10
6135090	D 1926		*	26	41.5	35.5	29.4	18.5	139	10
6135170	D 1927			27	41.5	36.7	30.0	18.5	143	10
6135250	D 1928		*	28	43.0	38.0	30.5	20.0	163	10
6135330	D 1929		*	29	43.0	39.2	31.2	20.0	168	10
6135410	D 1930			30	43.0	40.5	32.5	20.5	182	10
6135760	D 1932			32	44.5	43.0	34.5	22.5	204	10
6135840	D 1933		*	33	44.5	44.2	36.0	22.5	221	10
2545314	D 1934		*	34	44.5	45.5	37.0	22.5	251	10
2194686	D 1936		*	36	44.5	48.0	38.0	22.5	271	10

Code	No.	O AF	L	d ₁	d ₂	t	1/2"	£
6136060	D 19 5/16AF	5/16	38.0	13.0	22.5	7.0	52	5
6136140	D 19 11/32AF	11/32	38.0	13.9	22.5	8.0	54	5
6136220	D 19 3/8AF	3/8	38.0	14.9	22.5	15.0	55	5
6136300	D 19 13/32AF	13/32	38.0	15.9	22.5	13.5	55	5
6136490	D 19 7/16AF	7/16	38.0	16.7	22.5	12.5	56	5
6136570	D 19 1/2AF	1/2	38.0	18.7	22.5	12.5	58	5
6136650	D 19 9/16AF	9/16	38.0	20.7	22.5	12.5	61	5
6136730	D 19 19/32AF	19/32	39.5	21.7	23.8	15.0	70	5
6136810	D 19 5/8AF	5/8	39.5	22.5	23.8	15.0	73	5
6137030	D 19 11/16AF	11/16	39.5	24.7	22.5	17.0	66	5
6137110	D 19 3/4AF	3/4	40.0	26.7	24.2	17.0	84	5
6137380	D 19 25/32AF	25/32	40.0	27.7	25.3	17.0	90	5
6137460	D 19 13/16AF	13/16	41.5	28.5	25.7	18.5	97	5
6137540	D 19 7/8AF	7/8	41.5	30.6	26.5	18.5	105	5
6137620	D 19 15/16AF	15/16	41.5	32.6	28.3	18.5	126	5
6137700	D 19 1AF	1	41.5	34.6	28.9	18.5	138	5
6137890	D 19 1.1/16AF	1.1/16	41.5	36.7	30.0	18.5	147	5
6137970	D 19 1.1/8AF	1.1/8	43.0	38.6	31.0	20.0	159	5
6138000	D 19 1.3/16AF	1.3/16	43.0	40.6	32.5	20.5	183	5
6138190	D 19 1.1/4AF	1.1/4	44.5	42.6	34.5	22.5	207	10

Whitw.

Code	No.	O Whitw.	L	d ₁	d ₂	t	1/2"	£
6138780	D 19 3/16W	3/16	38.0	17.0	22.5	12.5	54	10
6138860	D 19 1/4W	1/4	38.0	19.5	22.5	12.5	57	10
6138940	D 19 5/16W	5/16	39.5	21.9	23.8	15.0	69	10
6139080	D 19 3/8W	3/8	39.5	25.5	23.0	17.0	66	10
6139160	D 19 7/16W	7/16	41.5	28.8	26.0	18.5	96	10
6139240	D 19 1/2W	1/2	41.5	32.1	27.8	18.5	124	10
6139320	D 19 9/16W	9/16	41.5	34.9	29.2	18.5	137	10
6139400	D 19 5/8W	5/8	43.0	37.8	30.5	20.0	166	10
6139590	D 19 11/16W	11/16	43.0	41.0	33.0	20.5	184	10
6138430	D 19 3/4W	3/4	44.5	44.2	36.0	22.5	225	10