



Connectors > Audio & Video Connectors > USB Connectors



USB Adapter Type: **A**

USB Version: **3.0**

Connector Profile: **Standard**

Connector & Housing Type: **Receptacle**

Number of Ports: **1**

Features

Product Type Features

USB Adapter Type	A
USB Version	3.0
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board
USB Connector Type	USB 3.0 Type-A

Configuration Features

Number of Ports	1
Number of Positions	4

Body Features

Connector Profile	Standard
-------------------	----------

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]

Mechanical Attachment

Locking Feature	Without
PCB Mount Location	Top
PCB Mount Retention Type	Boardlock

Housing Features

Housing Material	PA 9T GF
------------------	----------



Housing Color	Black
Body Orientation	Right Angle

Packaging Features

Packaging Method	Box & Tray, Tray
------------------	------------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Alcoswitch Gemini A



Toggle Switches(77)

Customers Also Bought



TE Part #2023246-2
ASS'Y SATA REC. R/A SMT TYPE 3.45H



TE Part #6450863-5
MBXLE VERT RCPT 7ACP



TE Part #5177984-6
0.8FH,P05H.5,140,08/Sn,TU



TE Part #2174507-2
MICRO USB, TYPE B



TE Part #1734366-3
Std USB Type A, VT, T/H, Blue



TE Part #2007435-3
Std HDMI, Flag, T/H



TE Part #1-1734035-2
MINI USB, TYPE B, R/A, SMT



TE Part #2110304-1
SFP+ 1x1 Cage Assembly, Solder Tail



TE Part #1-6450869-0
V/R
2ACP+8S+4ACP+16S+2ACP+12S+2ACP



TE Part #1747981-2
Std HDMI, RA, SMT

Documents

- CAD Files
- Customer View Model
- ENG_CVM_CVM_1932965-1_A.2d_dxf.zip
- English
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_1932965-1_A.3d_igs.zip

1932965-1

USB 3.0 A RECEPTACLE, OFFSET CL 2.65



English

Customer View Model

[ENG_CVM_CVM_1932965-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.