

General Information

Extended Product Type:	MS4/6
Product ID:	1SNA115265R2400
EAN:	3472591152654
Catalog Description:	MS4/6 Screw Clamp Terminal Blocks - Miniblocks - Grey
Long Description:	- Save space with compact over-all dimensions terminal block, - Flexibility: snap onto symmetrical and asymmetrical rails.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
CSA Certificate:	1SND161039A0201
Color:	Grey
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 10 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22 ... 10 AWG Stranded 10 AWG
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 4 mm ² Screw Clamp / Rigid 1x 0.2 ... 4 mm ²
Connection Type:	Screw clamp
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160020C0201
Declaration of Conformity - CE:	1SND225051U1000
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Dielectric Test Voltage:	2500 V
E-nummer:	2925504
EAC Certificate:	1SND161009A1100
EAN:	3472591152654
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220001E1002
Flammability According to UL94:	V0
Function:	Miniblock
Gauge Type:	A4
Gauge(s) of Form:	A4
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160020C0201
Insulation Material:	Polyamide
Invoice Description:	MS4/6 Screw Clamp Terminal Blocks - Miniblocks - Grey
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	100 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715

TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Number of Connections:	2
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	100 piece
Package Level 1 EAN:	3472591152654
Package Level 1 Gross Weight:	0.6 kg
Package Level 1 Height:	37 mm
Package Level 1 Length:	205 mm
Package Level 1 Units:	100 piece
Package Level 1 Width:	126 mm
Package Level 2 Gross Weight:	9.35 kg
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	1500 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	72000 piece
Pollution Degree:	3
Product Main Type:	MS4/6
Product Name:	Terminal block
Product Net Depth:	31 mm
Product Net Height:	41 mm
Product Net Weight:	6 g
Product Net Width:	6 mm
Product Packing Type:	Box
RMRS Certificate:	1SND161007A1101
Rated Cross-Section:	4 mm ²
Rated Current (I _n):	Main Circuit 32 A
Rated Impulse Withstand Voltage (U _{imp}):	4000 V
Rated Short-time Withstand Current (I _{cw}):	for 1 s 480 A
Rated Voltage (U _r):	630 V
Recommended Screw Driver:	4 mm
RoHS Date:	20050518
RoHS Information:	1SND230023F0208
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	grey Screw Clamp Terminal Blocks MS4/6
Spacing:	6 mm
Sub-Function:	Feed-through
Sub-Function 2:	For TH35 and G32 Rail
Sub-Function 3:	Rail mounting G32, TH 35-7.5, TH 35-15
Sub-Function 4:	Feed-through
Tightening Torque:	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m
Wire Stripping Length:	10.0 mm
cUL Certificate:	1SND161001A0209
Number of Potentials:	1

