





DUAL SURFACE MOUNT SWITCHING DIODE

Features


- Fast Switching Speed
- Ultra-Small Surface Mount Package
- For General Purpose Switching Applications
- High Conductance
- Lead Free/RoHS Compliant (Note 3)
- "Green" Device (Notes 4 and 5)

Mechanical Data

- Case: SOT-323
- Case Material: Molded Plastic, "Green" Molding Compound, Note 5. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020D
- Terminals: Solderable per MIL-STD-202, Method 208
- Lead Free Plating (Matte Tin Finish annealed over Alloy 42 leadframe)
- Polarity: See Diagram
- Marking Information: See Page 3
- Ordering Information: See Page 3
- Weight: 0.006 grams (approximate)

SOT-323





Maximum Ratings @T_A = 25°C unless otherwise specified

Characteristic		Symbol	Value	Unit
Non-Repetitive Peak Reverse Voltage		V_{RM}	100	V
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		V _{RRM} V _{RWM} V _R	75	٧
RMS Reverse Voltage		V _{R(RMS)}	53	V
Forward Continuous Current (Note 1)		I _{FM}	300	mA
Average Rectified Output Current (Note 1)		lo	150	mA
Non-Repetitive Peak Forward Surge Current (Note 1)	@ t = 1.0μs @ t = 1.0s	I _{FSM}	2.0 1.0	А

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 1)	P_{D}	200	mW
Thermal Resistance Junction to Ambient Air (Note 1)	$R_{ hetaJA}$	625	°C/W
Operating and Storage Temperature Range	T_J , T_{STG}	-65 to +150	°C


Electrical Characteristics @T_A = 25°C unless otherwise specified


Characteristic	Symbol	Min	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 2)	$V_{(BR)R}$	75	_	V	$I_R = 2.5 \mu A$
Forward Voltage	Ve	_	0.715 0.855	V	I _F = 1.0mA I _F = 10mA
	.,		1.0 1.25		I _F = 50mA I _F = 150mA
Reverse Current (Note 2)	I _R	_	2.5 50 30 25	μΑ μΑ μΑ nA	$V_R = 75V$ $V_R = 75V$, $T_J = 150^{\circ}C$ $V_R = 25V$, $T_J = 150^{\circ}C$ $V_R = 20V$
Total Capacitance	C _T	_	2.0	pF	$V_R = 0, f = 1.0MHz$
Reverse Recovery Time	t _{rr}	_	4.0	ns	$I_F = I_R = 10 \text{mA},$ $I_{rr} = 0.1 \times I_R, R_L = 100 \Omega$

Notes:

- Device mounted on FR-4 PC board with recommended pad layout, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.
- 2. Short duration pulse test used to minimize self-heating effect.
- No purposefully added lead.
- 4. Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead_free/index.php.
- 5. Product manufactured with Date Code 0627 (week 27, 2006) and newer are built with Green Molding Compound. Product manufactured prior to Date Code 0627 are built with Non-Green Molding Compound and may contain Halogens or Sb2O3 Fire Retardants.











Fig. 5 Reverse Recovery Time vs. Forward Current, Per Element



V_F, INSTANTANEOUS FORWARD VOLTAGE (V) Fig. 2 Typical Forward Characteristics, Per Element




Fig. 4 Total Capacitance vs. Reverse Voltage, Per Element




Ordering Information (Notes 5 & 6)

Part Number	Case	Packaging
BAW56W-7-F	SOT-323	3000/Tape & Reel

Notes:

6. For packaging details, go to our website at http://www.diodes.com/datasheets/ap02007.pdf.

Marking Information




KJC = Product Type Marking Code YM = Date Code Marking Y = Year ex: N = 2002 M = Month ex: 9 = September

Date Code Key


Year	2000	2001	2002	2003	2004	2005	2006	2007	2008	2009	2010	2011	2012
Code	L	М	N	Р	R	S	Т	U	V	W	Х	Y	Z
Month	Jan	Feb	Mar	Apr	r Ma	y J	un	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5		6	7	8	9	0	Ν	D

Package Outline Dimensions



SOT-323					
Dim	Min	Max			
Α	0.25	0.40			
В	1.15	1.35			
С	2.00	2.20			
D	0.65 Nominal				
F	0.30 0.40				
G	1.20	1.40			
Н	1.80	2.20			
J	0.0 0.10				
K	0.90 1.00				
L	0.25 0.40				
M	0.10	0.18			
α	0°	8°			
All Dimensions in mm					

Suggested Pad Layout



Dimensions	Value (in mm)
Z	2.8
Х	0.7
Υ	0.9
С	1.9
Е	1.0

IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.