

### Main

Range	TransferPacT
Range of product	PrismaSeT P
Device short name	TP
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT P TP mounting plate
Installation description	Cubicle - width 650 + 150 mm depth 400 mm Cubicle - width 650 mm
Enclosure mounting	Surface
Mounting location	Top and bottom front of enclosure
Mounting plate description	Dedicated
Type of rail	Modular
Installed device	Fixed with earth leakage protection - vertical installation
Poles description	1 x 3P or 4P: panel mounting terminal blocks vertical installation
Condition of using cable tie	-20-70 °C (8M high) when installation of device is in vertical
Number of vertical modules [50 mm]	8 module(s): terminal blocks integrated earth leakage protection , comb busbar in 650 + 150 mm Wide2 floor-standing enclosure (cable coming from top and bottom of enclosure) 8 module(s): terminal blocks integrated earth leakage protection , comb busbar in 650 mm Wide2 floor-standing enclosure + duct (cable coming from top and bottom of enclosure)
Standards	IEC 61439-2
Product certifications	IEC

### Complementary




Connections - terminals	4 screw terminals terminal blocks switch
Cable entry	Top and bottom 0...70 mm in front of support frame
Material	On mounting holes: stainless steel
Protective treatment	None
Width	570 mm
Height	247 mm
Depth	16 mm
Net weight	2 kg
Quantity per set	1 kit

### Environment

IP degree of protection	> IP31 0...50 °C conforming to IEC 61439-2
IK degree of protection	IK10 conforming to IEC 60947
Mechanical robustness	IK protection 25...55 °C, RH 95 % - - 20...55 °C conforming to IEC 61439-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company mentioned herein. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations