



### Main

Range of product	KNX
Product or component type	Control unit 0-10 V
Operating mode	KNX bus system Manual
Bus type	KNX

### Complementary

Total number of 18 mm modules	4
Mounting support	DIN rail
[Ue] rated operational voltage	100...240 V AC 50...60 Hz
Input current	0.12...100 mA
Analogue output type	Voltage
Analogue output range	1...10 V
Number of outputs	3
[In] rated current	16 A
Load type	Incandescent lamps: ≤ 1600 W, 100 V AC Incandescent lamps: ≤ 3600 W, 230 V AC Incandescent lamps: ≤ 3840 W, 240 V AC Halogen lamps: ≤ 1086 W, 100 V AC Halogen lamps: ≤ 2500 W, 230 V AC Halogen lamps: ≤ 2608 W, 240 V AC Parallel compensated fluorescent lamp: ≤ 1086 VA, 100 V AC Parallel compensated fluorescent lamp: ≤ 2500 VA, 230 V AC Parallel compensated fluorescent lamp: ≤ 2608 VA, 240 V AC Capacitive: , 16 A, 200 µF, 100...240 V AC

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins