

Technical data


2301S

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	12 mm
D - External diameter	37 mm
B - Bearing/Inner ring width	17 mm
rs - Min fillet radius	1 mm
Radial clearance class	CN
Precision class	P0
Mass	0,087 kg

PRODUCT PERFORMANCE

C - Dynamic load	12100000 mN
C0 - Static load	2730000 mN
Cu - Fatigue limit load	120000 mN
e - Coefficient	0.6
Y0 - Static axial load coefficient	1.1
Y1 - Lower axial load coefficient	1.1
Y2 - Upper axial load coefficient	1.6
N lim - Oil lubrication limit speed	132000 °/s
N lim - Grease lubrication limit speed	102000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	17 mm
Da max - Max shoulder diameter OR	32 mm



2301S
Double-row self-aligning ball bearings

ABUTMENT	
ra max - Max shaft & housing fillet radius	1 mm