

Applicant : Calpe B.V.
De Fliert 3
3791 PV ACHTERVELD
Netherlands

Application date : 97-06-05

Order number : 97.2616.01-KRQ/HCA

Subject : type-test flush type signal
lamps

Tradename : CALPE

Series : 3000

Type : 07-3130-....., 07-3135-.....,
07-3160-....., 07-3161-.....,
07-3220-....., 07-3221-.....

Arnhem, January 19, 1999

Manufacturer/factory-location:
Calpe B.V., De Fliert 3, 3791 PV Achterveld, Netherlands


Test requirements : EN 60598-2-1, 1989

The KEMA test requirements, K43C-2-30, are taken into account.

Conclusion : the products comply with the specified requirements.

Tested by : H.H.M. Versteegen

Checked by : A.P. van der Veen



Vsn/MJH

99-1374

Products may only be provided with an approval mark if the relevant conditions have been fulfilled.

* Publication in total or in part and/or reproduction in whatever way of the contents of this report is not allowed unless permission has been explicitly given either in this report or by previous letter.

N.V. KEMA and/or its affiliates disclaim liability for any direct, indirect, consequential or incidental damages that may result from the use of the information or data, or from the inability to use the information or data.

KEMA Nederland B.V. Utrechtseweg 310, 8812 AR Arnhem, the Netherlands
P.O. box 9035, 6800 ET ARNHEM, the Netherlands.
Telephone +31 26 3 56 25 22. Telefax +31 26 3 51 49 22.

Product data:

types : 07-3130-.-., 07-3135-.-.,
07-3160-.-., 07-3161-.-.,
07-3220-.-., 07-3221-.-.

tradename : CALPE

rated voltage : 120 V, 230 V, 400 V, 440 V

nature of supply : ac

rated frequency : 50 Hz

rated lamp power : 0,5 W

Further data:

- intended to be mounted in class I or Class II appliances.
- with pillar terminals for solid wiring 0.75 mm² to 1.5 mm² or flexible wiring provided with wire protectors.
- to be mounted and connected according to the instructions on the sticker on the packing.

Product details

The type designation consists of the number 3 with a prefix 07, followed by suffixes.

1st suffix concerning the diameter

13 = 13 mm
16 = 16 mm
22 = 22 mm

2nd suffix for the design, colour or finish, plating of the ring and adaptor**3rd suffixed for the lens colour**

1 = red
3 = green fluorescent
4 = yellow
5 = clear
6 = white
8 = blue fluorescent

4th suffix for the rated voltage

120 = 120 Vac
230 = 230 Vac
400 = 400 Vac
440 = 440 Vac

Product data per type covered by this report:**07-3130-.-...****maximum temperature : 120 °C****07-3135-.-...****maximum temperature : 55 °C****07-3160-.-...****maximum temperature : 120 °C****07-3161-.-...****maximum temperature : 55 °C****07-3220-.-...****maximum temperature : 120 °C****07-3221-.-...****maximum temperature : 120 °C**