




---

 PRODUCT-DETAILS

# AF140B-40-22-14

## AF140B-40-22-14 Contactor




---

**General Information**

Extended Product Type	AF140B-40-22-14
Product ID	1SFL447263R1422
EAN	7320500511350
Catalog Description	AF140B-40-22-14 Contactor
Long Description	A 4-pole contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 690 V. Operated with 250 ... 500 V, 50Hz/60Hz and DC. Equipped with 2 N.O and 2 N.C. auxiliary contacts.

---

**Ordering**

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

---

**Popular Downloads**

Data Sheet, Technical Information	1SBC100214C0202
Data Sheet, Technical	1SAC200017M0002

Information (Part 2)

Instructions and Manuals	1SFC100003M0201
CAD Dimensional Drawing	2CDC001079B0201

**Dimensions**

Product Net Width	120 mm
Product Net Depth / Length	128 mm
Product Net Height	150 mm
Product Net Weight	2.05 kg

**Technical**

Number of Main Contacts NO	4
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	2
Number of Auxiliary Contacts NC	2
Number of Poles	4P
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50 / 60 Hz
Rated Operational Current AC-1 (I <sub>e</sub> )	(690 V) 40 °C 200 A (690 V) 60 °C 175 A (690 V) 70 °C 160 A
Rated Operational Current AC-3 (I <sub>e</sub> )	(415 V) 55 °C 140 A (440 V) 55 °C 140 A (380 / 400 V) 55 °C 140 A (220 / 230 / 240 V) 55 °C 140 A
Rated Operational Current DC-1 (I <sub>e</sub> )	(110 V) 2 Poles in Series, 40 °C 200 A (110 V) 2 Poles in Series, 60 °C 175 A (110 V) 2 Poles in Series, 70 °C 160 A (110 V) 3 Poles in Series, 40 °C 200 A (110 V) 3 Poles in Series, 60 °C 175 A (110 V) 3 Poles in Series, 70 °C 160 A (175 V) 2 Poles in Series, 40 °C 200 A (175 V) 2 Poles in Series, 60 °C 175 A (175 V) 2 Poles in Series, 70 °C 160 A (220 V) 3 Poles in Series, 40 °C 200 A (220 V) 3 Poles in Series, 60 °C 175 A (220 V) 3 Poles in Series, 70 °C 160 A (260 V) 3 Poles in Series, 40 °C 200 A (260 V) 3 Poles in Series, 60 °C 175 A (260 V) 3 Poles in Series, 70 °C 160 A (350 V) 4 Poles in Series, 40 °C 200 A (350 V) 4 Poles in Series, 60 °C 175 A (350 V) 4 Poles in Series, 70 °C 160 A (72 V) 1-Pole, 40 °C 200 A (72 V) 1-Pole, 60 °C 175 A (72 V) 1-Pole, 70 °C 160 A (72 V) 2 Poles in Series, 40 °C 200 A (72 V) 2 Poles in Series, 60 °C 175 A (72 V) 2 Poles in Series, 70 °C 160 A (72 V) 3 Poles in Series, 40 °C 200 A (72 V) 3 Poles in Series, 60 °C 175 A (72 V) 3 Poles in Series, 70 °C 160 A (90 V) 1 Pole, 40 °C 200 A

	(90 V) 1 Pole, 60 °C 175 A (90 V) 1 Pole, 70 °C 160 A
Rated Operational Current DC-3 (I <sub>e</sub> )	(110 V) 2 Poles in Series, 40 °C 160 A (110 V) 2 Poles in Series, 60 °C 160 A (110 V) 2 Poles in Series, 70 °C 160 A (110 V) 3 Poles in Series, 40 °C 160 A (110 V) 3 Poles in Series, 60 °C 160 A (110 V) 3 Poles in Series, 70 °C 160 A (220 V) 3 Poles in Series, 40 °C 160 A (220 V) 3 Poles in Series, 60 °C 160 A (220 V) 3 Poles in Series, 70 °C 160 A (72 V) 2 Poles in Series, 40 °C 160 A (72 V) 2 Poles in Series, 60 °C 160 A (72 V) 2 Poles in Series, 70 °C 160 A (72 V) 3 Poles in Series, 40 °C 160 A (72 V) 3 Poles in Series, 60 °C 160 A (72 V) 3 Poles in Series, 70 °C 160 A
Rated Operational Current DC-5 (I <sub>e</sub> )	(110 V) 2 Poles in Series, 40 °C 160 A (110 V) 2 Poles in Series, 60 °C 160 A (110 V) 2 Poles in Series, 70 °C 160 A (110 V) 3 Poles in Series, 40 °C 160 A (110 V) 3 Poles in Series, 60 °C 160 A (110 V) 3 Poles in Series, 70 °C 160 A (220 V) 3 Poles in Series, 40 °C 160 A (220 V) 3 Poles in Series, 60 °C 160 A (220 V) 3 Poles in Series, 70 °C 160 A (72 V) 2 Poles in Series, 40 °C 160 A (72 V) 2 Poles in Series, 60 °C 160 A (72 V) 2 Poles in Series, 70 °C 160 A (72 V) 3 Poles in Series, 40 °C 160 A (72 V) 3 Poles in Series, 60 °C 160 A (72 V) 3 Poles in Series, 70 °C 160 A
Rated Operational Power AC-3 (P <sub>e</sub> )	(415 V) 75 kW (440 V) 90 kW (500 V) 90 kW (690 V) 75 kW (380 / 400 V) 75 kW (220 / 230 / 240 V) 37 kW
Rated Breaking Capacity AC-3e	8.5 x I <sub>e</sub> AC-3e
Rated Making Capacity AC-3	10 x I <sub>e</sub> AC-3
Rated Making Capacity AC-3e	12 x I <sub>e</sub> AC-3e
Rated Short-time Withstand Current Low Voltage (I <sub>cw</sub> )	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 200 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 674 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 1460 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 1168 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 477 A
Rated Insulation Voltage (U <sub>i</sub> )	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V acc. to UL/CSA 600 V
Maximum Electrical Switching Frequency	(AC-1) 300 cycles per hour (AC-3) 300 cycles per hour
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) 0.85 x U <sub>c</sub> Min. ... 1.1 x U <sub>c</sub> Max. (at θ ≤ 70 °C)
Rated Control Circuit Voltage (U <sub>c</sub> )	50 Hz / 60 Hz 250 ... 500 V DC Operation 250 ... 500 V
Coil Consumption	Average Pull-in Value 50 Hz 260 V·A Average Pull-in Value 60 Hz 260 V·A Holding at Max. Rated Control Circuit Voltage 50 Hz 16.1 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 16.1 V·A Pull-in at Max. Rated Control Circuit Voltage 50 Hz 205 V·A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 205 V·A Pull-in at Max. Rated Control Circuit Voltage DC 230 V·A Pull-in at Max. Rated Control Circuit Voltage DC 230 W

Power Loss	18 W at Rated Operating Conditions per Pole 18 W
Connecting Capacity Main Circuit	Flexible 2 x 10 ... 70 mm <sup>2</sup> Rigid Cu-Cable 2 x 10 ... 95 mm <sup>2</sup>
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 2x 0.75 ... 2.5 mm <sup>2</sup> Flexible with Insulated Ferrule 2x 0.75 ... 2.5 mm <sup>2</sup> Flexible 2x0.75 ... 2.5 mm <sup>2</sup> Solid 2 x 1 ... 4 mm <sup>2</sup> Stranded 2 x 1 ... 4 mm <sup>2</sup>
Connecting Capacity	Flexible 2 x 10 ... 70 mm <sup>2</sup> Rigid Cu-Cable 2 x 10 ... 95 mm <sup>2</sup>
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP40 acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Tightening Torque	Cable Lug 9 N·m
Terminal Type	Main Circuit: Bars
Product Name	Block Contactor

## Technical UL/CSA

NEMA Size	4
Continuous Current Rating NEMA	135 A
Horsepower Rating NEMA	(200 V AC) Three Phase 40 Hp (230 V AC) Three Phase 50 Hp (460 V AC) Three Phase 100 Hp (575 V AC) Three Phase 100 Hp
Maximum Operating Voltage UL/CSA	Main Circuit 600 V
General Use Rating UL/CSA	(600 V AC) 175 A
Horsepower Rating UL/CSA	(200 ... 208 V AC) Three Phase 15 Hp (200 V AC) Three Phase 40 hp (208 V AC) Three Phase 40 hp (220 ... 240 V AC) Three Phase 20 Hp (220 ... 240 V AC) Three Phase 50 hp (440 ... 480 V AC) Three Phase 40 Hp (440 ... 480 V AC) Three Phase 100 hp (550 ... 600 V AC) Three Phase 50 Hp (550 ... 600 V AC) Three Phase 125 hp

## Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... 50 °C Close to Contactor for Storage -40 ... 70 °C
Maximum Operating Altitude Permissible	Without Derating 3000 m

## Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	No declaration needed
Toxic Substances Control Act - TSCA	2CMT2023-006525

WEEE B2C / B2B

Business To Business

WEEE Category

5. Small Equipment (No External Dimension More Than 50 cm)

## ABB EcoSolutions

ABB EcoSolutions	Yes
ABB Site Meeting Group Waste To Landfill Target	Non-hazardous waste is sent to a landfill, where there is no alternative option available within 100km of a facility
End Of Life Disassembling Instructions	1SFC100112M0001
Environmental Product Declaration - EPD	1SFC100092D0201
Improved Energy Efficiency for Customers	Product Efficiency - Product requires less energy to operate compared to similar product on market or older products from the same line
Recyclability Rate of the Product acc. to EN45555	Design for Closing Resource Loops - Standard EN45555 - 87.8 %
Sustainable Material Content in Product (wt. %)	Recycled Metal - 37 %

## Certificates and Declarations

CB Certificate	SEMKO_SE-77317
CQC Certificate	CQC2013010304604055
Declaration of Conformity - CCC	2020980304001304
Declaration of Conformity - CE	2CMT2015-005440
Declaration of Conformity - UKCA	2CMT2020-006124
EAC Certificate	9AKK107046A8618
KC Certificate	9AKK107046A9911
UL Certificate	E73397_20140710

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	147 mm
Package Level 1 Depth / Length	197 mm
Package Level 1 Height	155 mm
Package Level 1 Gross Weight	2.25 kg
Package Level 1 EAN	7320500511350

## External Classifications and Standards

Object Classification Code	Q
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 8	EC000066 - Power contactor, AC switching
ETIM 9	EC000066 - Power contactor, AC switching
eClass	V11.0 : 27371003
UNSPSC	39121529

IDEA Granular Category  
Code (IGCC)

4755 >> Contactors

E-Number (Sweden)

3210467

---

## Categories

---

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors → AF Contactors → AF140

