



06151035

RCK 15 - Self centring

2D Technical Drawing

Dynamic 3D View

Technical Specifications

Part number (CODE)	06151035
Ød (DD) mm	35
ØD (D) mm	65
L1 (L1) mm	17
L2 (L2) mm	22
L3 (L3) mm	31
L (L) mm	39
Maximum torque Mt (MT) Nm	900
Clamping pressure - Shaft (CPS) N/mm ²	228
Clamping pressure - Hub (CPH) N/mm ²	122
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	5
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M8x25
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	41
Extraction thread - Type (ETT)	M8
Extraction thread - Num. (ETN)	3
Weight (WEIGHT) kg	0.50