

Product datasheet

Specifications



TeSys GC - modular contactor - 40 A - 4 NC - coil 220...240 V AC

Local distributor code:

23049831

GC4004M5

EAN Code: 3389110641936

Main

Range	TeSys
Product name	TeSys GC
Product or component type	Modular contactor
Device short name	GC40
Contactor application	Lighting Heating Motor control

Complementary

Utilisation category	AC-7B AC-7A
Poles description	4P
power pole contact composition	4 NC
[Ue] rated operational voltage	<= 250 V AC
[Ie] rated operational current	40 A AC-7A 15 A AC-7B
Operating position	30°/vertical
Control circuit type	AC at 50 Hz
[Uc] control circuit voltage	220...240 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
[Ith] conventional free air thermal current	40 A (at 50 °C) for power circuit
Irms rated making capacity	120 A at 400 V AC for power circuit conforming to IEC 61095
Rated breaking capacity	120 A at 400 V for power circuit conforming to IEC 61095
[Icw] rated short-time withstand current	320 A 40 °C - 10 s for power circuit 100 A 40 °C - 30 s for power circuit
Associated fuse rating	40 A gL at <= 440 V for power circuit
Average impedance	2 mOhm - Ith 40 A 50 Hz for power circuit
[Ui] rated insulation voltage	500 V conforming to IEC 61095 500 V conforming to VDE 0110
Electrical durability	AC-7A: 100000 cycles AC-7B: 100000 cycles
Power dissipation per pole	3.2 W
Control type	Remote control
Mounting mode	Clip-on
Mounting support	DIN rail

Standards	IEC 61095 IEC 60947-5
Connections - terminals	Control circuit: screw clamp terminals 1 cable(s) 2.5 mm ² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 2.5 mm ² flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 2.5 mm ² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm ² flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 1.5 mm ² solid without cable end Control circuit: screw clamp terminals 2 cable(s) 1.5 mm ² solid without cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm ² flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 16 mm ² flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 16 mm ² flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 4 mm ² flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 25 mm ² solid without cable end Power circuit: screw clamp terminals 2 cable(s) 6 mm ² solid without cable end
Tightening torque	Control circuit: 0.8 N.m - on screw clamp terminals Power circuit: 2 N.m - on screw clamp terminals
Operating time	10...25 ms opening 10...30 ms closing
Mechanical durability	1000000 cycles
Maximum operating rate	300 cyc/h 50 °C
Control circuit voltage limits	Drop-out: 0.2...0.75 Uc at 50 Hz (at <50 °C) Operational: 0.85...1.1 Uc at 50 Hz (at <50 °C)
Inrush power in VA	53 VA 50 Hz (at 20 °C)
Hold-in power consumption in VA	6.5 VA 50 Hz (at 20 °C)
Heat dissipation	2.1 W at 50/60 Hz

Environment

IP degree of protection	IP40 conforming to VDE 0106 (in enclosure) IP20 conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m
Mechanical robustness	Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms Vibrations contactor open: 2 Gn, 5...300 Hz Vibrations contactor closed: 3 Gn, 5...300 Hz
Total number of 18 mm modules	3
Height	85 mm
Width	54 mm
Depth	62.5 mm
Net weight	0.39 kg
Quantity per set	Set of 4
Colour	White

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.400 cm
Package 1 Width	6.800 cm

Package 1 Length	8.900 cm
Package 1 Weight	322.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	8.300 cm
Package 2 Width	9.600 cm
Package 2 Length	23.000 cm
Package 2 Weight	1.358 kg
Unit Type of Package 3	S03
Number of Units in Package 3	32
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	11.585 kg

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 106

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

SCIP Number 602f090b-0363-4125-8a1d-b0ae6265ecec

REACH Regulation [REACH Declaration](#)

Halogen-free status Halogen free plastic parts product

Use Longer

Lifetime extension

Repair No

Use Again

Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins