



Technical data

4T-LM12749/LM12711

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage

KIT CONTENT


4T-LM12749, 4T-LM12711

VISUAL (S)



4T-LM12749/LM12711

Single row tapered roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	21,986 mm
D - External diameter	45,974 mm
B - Bearing/Inner ring width	16,637 mm
C - Outer ring width	12,065 mm
T - Total width	15,494 mm
d1 - External diameter inner ring	34 mm
a - Charge load application point	10,094 mm
rs - Min fillet radius	1,3 mm
r1s - Min fillet radius	1,3 mm
Mass	0,123 kg

PRODUCT PERFORMANCE

C - Dynamic load	29600000 mN
------------------	-------------



4T-LM12749/LM12711

Single row tapered roller bearings

PRODUCT PERFORMANCE

C0 - Static load	34000000 mN
Cu - Fatigue limit load	4150000 mN
A2 - Rating life coefficient	1
e - Coefficient	0.31
Y0 - Static axial load coefficient	1.08
Y2 - Upper axial load coefficient	1.96
N lim - Oil lubrication limit speed	66000 °/s
N lim - Grease lubrication limit speed	50400 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da max - Max shoulder diameter IR	26 mm
db min - Min IR shoulder diameter	27,5 mm
Da max - Max shoulder diameter OR	40 mm
Db min - Min OR shoulder diameter	42,5 mm
ra max - Max fillet radius	1,3 mm
r1a - Max fillet radius	1,3 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

