



FX3-MOC000000

Flexi Soft Drive Monitor

SAFE MOTION

SICK
Sensor Intelligence.




Ordering information

Motion Control module

| Description | Type | Part no. |
|-----------------------|---------------|----------|
| Safe speed monitoring | FX3-MOC000000 | 1062344 |

Other models and accessories → www.sick.com/Flexi_Soft_Drive_Monitor



Detailed technical data

Features

| | |
|-----------------------------|------------------------------------|
| Module | Motion Control module |
| Configuration method | Via software (Flexi Soft Designer) |

Safety-related parameters

For axes with two encoders (any combination of sine-cosine, TTL, HTL 24 V, MTL 12 V, RS-422, SSI)

| | |
|---|---|
| Safety integrity level | SIL3 (IEC 61508) SILCL3 (EN 62061) |
| Category | Category 4 (EN ISO 13849) |
| Performance level | PL e (EN ISO 13849) |
| PFH_D (mean probability of a dangerous failure per hour) | 5.0×10^{-9} |
| Minimum movement for error detection | \geq selected tolerance limit for the function block used for the cross check, e.g. speed cross check, At least 1 x within 24 h |
| T_M (mission time) | 20 years (EN ISO 13849) |

For axes with one sine-cosine encoder and sin/cos analog voltage monitoring activated

| | |
|---|---|
| Safety integrity level | SIL2 (IEC 61508) SILCL2 (EN 62061) |
| Category | Category 3 (EN ISO 13849) |
| Performance level | PL d (EN ISO 13849) |
| PFH_D (mean probability of a dangerous failure per hour) | 6.0×10^{-9} |
| Minimum movement for error detection | ≥ 1 Sin/Cos period, At least 1 x within 24 h |
| T_M (mission time) | 20 years (EN ISO 13849) |

Functions

| | |
|-------------------------------|--|
| Drive safety functions | Safe stop 1 (SS1) Safe stop 2 (SS2) Safe operating stop (SOS) Safe speed monitoring (SSM) |
|-------------------------------|--|

| | |
|--|--|
| | Safely-limited speed (SLS) Safe direction (SDI) Safe brake control (SBC) |
|--|--|

Interfaces

| | |
|--------------------------|--|
| Encoder interface | A/B incremental encoder, TTL A/B incremental encoder, HTL 12 V or 24 V A/B incremental encoder, RS-422 Sin/cos encoder SSI encoder (master / listener) HIPERFACE® |
| Connection type | Male connector, Micro D-Sub, 15-pin |
| Data interface | Internal bus (FLEXBUS+) |

Electrical data

| | |
|--|---|
| Protection class | III (EN 61140) |
| Voltage supply | Via FLEXBUS+ |
| Internal power consumption | ≤ 2.5 W ¹⁾ |
| A/B incremental encoder, TTL, 2 outputs | <p>Differential input voltage HIGH 5 V (2 V ... 5.3 V)²⁾</p> <p>Differential input voltage LOW 0 V (-0.3 V ... 0.8 V)²⁾</p> <p>Input voltage -5 V ... 10 V³⁾</p> <p>Input frequency ≤ 300 kHz</p> <p>Input resistance ≥ 35 kΩ</p> |
| A/B incremental encoder, TTL, 2 pairs of outputs | <p>Differential input voltage HIGH 5 V (1.2 V ... 5.6 V)²⁾</p> <p>Differential input voltage LOW -5 V (-5.6 V ... -1.2 V)²⁾</p> <p>Input voltage -5 V ... 10 V³⁾</p> <p>Input frequency ≤ 300 kHz</p> <p>Input resistance ≥ 35 kΩ</p> |
| A/B incremental encoder, HTL 12 V, 2 outputs | <p>Differential input voltage HIGH 12 V (6.5 V ... 15 V)²⁾</p> <p>Differential input voltage LOW 0 V (-1 V ... 2.5 V)²⁾</p> <p>Input voltage -5 V ... 20 V³⁾</p> <p>Input frequency ≤ 300 kHz</p> <p>Input resistance ≥ 35 kΩ</p> |
| A/B incremental encoder, HTL 12 V, 2 pairs of outputs | <p>Differential input voltage HIGH 12 V (4 V ... 15 V)²⁾</p> <p>Differential input voltage LOW -12 V (-15 V ... -4 V)²⁾</p> |

¹⁾ Via FLEXBUS+, without streams at analog inputs.²⁾ Voltage between ENC_x_y+ and ENC_x_y-.³⁾ Voltage between ENC_x_y+ and ENC_OV and between ENC_x_y- and ENC_OV.⁴⁾ Peak to peak voltage between ENC_x_y+ and ENC_x_y-.

| | | |
|--|--|--------------------------------------|
| | Input voltage | -5 V ... 20 V ³⁾ |
| | Input frequency | ≤ 300 kHz |
| | Input resistance | ≥ 35 kΩ |
| A/B incremental encoder, HTL 24 V, 2 outputs | | |
| | Differential input voltage HIGH | 24 V (13 V ... 30 V) ²⁾ |
| | Differential input voltage LOW | 0 V (-3 V ... 5 V) ²⁾ |
| | Input voltage | -10 V ... 40 V ³⁾ |
| | Input frequency | ≤ 300 kHz |
| | Input resistance | ≥ 35 kΩ |
| A/B incremental encoder, HTL 24 V, 2 pairs of outputs | | |
| | Differential input voltage HIGH | 24 V (8 V ... 30 V) ²⁾ |
| | Differential input voltage LOW | -24 V (-30 V ... -8 V) ²⁾ |
| | Input voltage | -10 V ... 40 V ³⁾ |
| | Input frequency | ≤ 300 kHz |
| | Input resistance | ≥ 35 kΩ |
| A/B incremental encoder, RS-422 | | |
| | Differential input voltage HIGH | 0.2 V ... 5 V ²⁾ |
| | Differential input voltage LOW | -5 V ... -0.2 V ²⁾ |
| | Input voltage | -7 V ... 7 V ³⁾ |
| | Input frequency | ≤ 1,000 kHz |
| | Input resistance | ≥ 35 kΩ |
| | Differential resistance | 120 Ω (100 Ω ... 150 Ω) |
| Sin/cos encoder | | |
| | Differential input voltage | 1 V (0.8 V ... 1.2 V) ⁴⁾ |
| | Input voltage | 0 V ... 5 V ³⁾ |
| | Input frequency | ≤ 120 kHz |
| | Input resistance | 1 kΩ (0.9 kΩ ... 1.1 kΩ) |
| Voltage monitoring, lower limit for vector length monitoring | | 0.5 V |
| Voltage monitoring, upper limit for vector length monitoring | | 1.5 V |
| SSI encoder (master / listener) | | |
| | Differential resistance | 120 Ω (100 Ω ... 150 Ω) |
| | Clock frequency | 100 kHz ... 1,000 kHz |
| | Cycle gaps between the data packages (monoflop time) | ≥ 100 μs |
| | Position data bits per frame | 16 ... 62 |

¹⁾ Via FLEXBUS+, without streams at analog inputs.²⁾ Voltage between ENC_x_y+ and ENC_x_y-.³⁾ Voltage between ENC_x_y+ and ENC_OV and between ENC_x_y- and ENC_OV.⁴⁾ Peak to peak voltage between ENC_x_y+ and ENC_x_y-.

Mechanical data

| | |
|-------------------------------|----------------------------|
| Dimensions (W x H x D) | 22.5 mm x 96.5 mm x 126 mm |
| Weight | 120 g |

Ambient data


| | |
|--------------------------------------|-------------------------------|
| Enclosure rating | IP20 (EN 60529) |
| Ambient operating temperature | -25 °C ... +55 °C |
| Storage temperature | -25 °C ... +70 °C |
| Air humidity | 10 % ... 95 %, Non-condensing |

Classifications

| | |
|-----------------------|----------|
| ECI@ss 5.0 | 27243001 |
| ECI@ss 5.1.4 | 27243101 |
| ECI@ss 6.0 | 27243101 |
| ECI@ss 6.2 | 27243101 |
| ECI@ss 7.0 | 27243101 |
| ECI@ss 8.0 | 27243101 |
| ECI@ss 8.1 | 27243101 |
| ECI@ss 9.0 | 27243101 |
| ECI@ss 10.0 | 27243101 |
| ECI@ss 11.0 | 27243101 |
| ETIM 5.0 | EC001449 |
| ETIM 6.0 | EC001449 |
| ETIM 7.0 | EC001449 |
| UNSPSC 16.0901 | 32151705 |


Dimensional drawing (Dimensions in mm (inch))

FX3-MOC0, FX3-MOC1



PIN assignment

FX3-MOC0, FX3-MOC1



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations www.sick.com