



EN ISO 20345:2011


 RESOLUTE  
**FORZA**  
 43452-11L

**S3 SRC \*CI AVAILABLE**
**Size:** 36-48  
**Weight:** 600 gr.

**Fit:** 11

**Working Environment:**  
 Multipurpose, Logistics and Light Industry, Components and Automotive, ESD Areas


## FEATURES

### UPPER

MicroFiber Rubber with Scratch Bumper 1,8-2,0 mm

### LINING

3D Green Air 320 gr.

### ANTISLIP LINING

DUALMICRO

### INSOLE

Qrs01

### TOE CAP

Fiber cap SXT

### RESISTANCE TO PERFORATION

KX Antiperforation PS

### TYPE

Low Shoe

### SOLE

**PU / PU ESD-PLUS SRC**

Double density PU sole, Outer- and in-between sole with ESD compound. For use in contact with sensitive electronic equipment. Light and comfortable, very versatile, highly non-slip SRC Antislip standard.

## TECHNOLOGIES

### Removable Insole



Anatomical breathable insole. Resistant fabric with recycled open-cell foam that absorbs shocks and reduces fatigue. Eliminates sweat with its high ability to evaporate it. Continuous comfort for months and months of use



### Protection elements



Composite toecap with fiberglass. Resistant to over 200J. Non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



### Lateral stability

**dynamic HC control**  
 technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



### Torsional stability

**STABIL•ACTIVE**

Support made of rigid plastic material. It supports the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.



### Electrical features



ESD footwear discharge static electricity and avoid damaging surrounding objects; they are designed in compliance with the following standards: IEC EN 61340-5-1:2016 - IEC EN 61340-4-3:2018 - IEC EN 61340-4-5:2018.

### Other

**D30**  
 PROGRESSIVE CUSHIONING AND ADAPTIVE STABILITY

D30 materials are made using a combination of advanced polymer chemistry and cutting-edge science. It absorbs and dissipates energy during and impact, with superior stability, cushioning and anti-fatigue effect.



## SRC (SRA+SRB)


 SOLE 43  
 PU - PU

|                                                     |                                                      |             |
|-----------------------------------------------------|------------------------------------------------------|-------------|
| <b>SRA</b><br>CERAMIC<br>+<br>DETERGENT<br>SOLUTION | FLAT<br>≥0.32<br>HEEL<br>(CONTACT ANGLE °°)<br>≥0.28 | <b>0.39</b> |
| <b>SRB</b><br>STEEL<br>+<br>GLYCEROL                | FLAT<br>≥0.18<br>HEEL<br>(CONTACT ANGLE °°)<br>≥0.13 | <b>0.24</b> |
|                                                     |                                                      | <b>0.23</b> |

EN ISO 20344:2011