
KEMET Part Number: T491A335K016AT



T491, Tantalum, MnO2 Tantalum, 3.3 uF, 10%, 16 VDC, SMD, MnO2, Molded, 5 Ohms, 3216, Height Max = 1.8mm



General Information	
Supplier:	KEMET
Series:	T491
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, MnO2, Molded
RoHS:	Yes
Termination:	Tin
Shelf Life:	156 Weeks
MSL:	1

Dimensions		
Footprint	3216	
L	3.2mm +/-0.2mm	
W	1.6mm +/-0.2mm	
Н	1.6mm +/-0.2mm	
Т	0.13mm REF	
S	0.8mm +0.2/-0.3mm	
F	1.2mm +/-0.1mm	
Α	1.2mm MIN	
В	0.4mm +/-0.15mm	
E	1.3mm REF	
G	1.1mm REF	
Р	0.4mm REF	
R	0.4mm REF	
Х	0.1mm +/-0.1mm	

Specifications	
Capacitance:	3.3 uF
Capacitance Tolerance:	10%
Voltage DC:	16 VDC (85C), 10.72 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85°C
Dissipation Factor:	6.00% 120Hz 20C
Failure Rate:	N/A
Resistance:	5 Ohms (100kHz)
Ripple Current:	122 mAmps (100kHz 25C), 109.8 mAmps (85C), 48.8 mAmps (125C)
Leakage Current:	0.5 uA (5min 20C)

Packaging Specifications		
Weight:	58.6 mg	
Packaging:	T&R, 178mm	
Packaging Quantity:	2000	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

