

Eaton 266836

Catalog Number: 266836

Eaton Moeller series NZM - Molded Case Circuit Breaker. Tunnel terminal, 3p, 1 switch side, size 4

General specifications



Product Name

Eaton Moeller series NZM connection
type

Catalog Number

266836

EAN

4015082668365

Product Length/Depth

88 mm

Product Height

90 mm

Product Width

159 mm

Product Weight

2.529 kg

Compliances

UL/CSA
IEC
RoHS conform

Certifications

CSA (Class No. 1432-01)
CE marking
UL listed
UL (Category Control Number DIHS)
UL (File No. E31593)
CSA certified
UL489
IEC60947
CSA (File No. 22086)
CSA-C22.2 No. 5-09

Product specifications

Used with

NZM4, N(S)4

Type

Accessory

Tunnel terminal

Amperage Rating

1400 A

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be

Resources

Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM4](#)

Drawings

[eaton-circuit-breaker-terminals-nzm-tunnel-terminal-dimensions-003.eps](#)

[eaton-circuit-breaker-terminals-nzm-tunnel-terminal-3d-drawing-005.eps](#)

Installation instructions

[eaton-circuit-breaker-nzm4-tunnel-flat-conductor-terminal-nzm4-4-xka-xkb-instruction-leaflet-il01210012z.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[nzm4_xka](#)

[nzm4_xka.stp](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Frame

NZM4

Suitable for

Three-pole

Copper cable

Number of poles

Three-pole

Model

Other

Terminal capacity (stranded cable)

50 mm² - 240 mm² (4x)

Max. 500 AWG/kcmil (4x)

Max. 500 AWG/kcmil (1x)

50 mm² - 240 mm² (1x)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia