

Rittal – The System.

Faster – better – everywhere.

Cable gland HD – HD 2410.131

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Cable gland HD – HD 2410.131

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Design:	EMC
Benefits:	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications:	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material:	Nut: Stainless steel 1.4305 (AISI 303) Seal: Conforms to FDA 21 CFR 177.2600
Protection category IP to IEC 60 529:	IP69 / IPX8 (5 bar, 30 min)
Supply includes:	Lock nut

Product description

Ambient temperature range:	-20 °C...+100 °C
Thread:	M25 x 1.5
Operating temperature (max.):	100 °C
Cable entry:	For cable diameter: 12 mm - 17 mm
Packs of:	5 pc(s).

Weight/pack:	0.88 kg
EAN:	4028177928664
Customs tariff number:	73181900
ETIM 7.0:	EC000441
ETIM 6.0:	EC000441
eCl@ss 8.0/8.1:	27149109
eCl@ss 6.0/6.1:	27189265
Product description:	HD Cable gland, stainless steel 1.4305, size: M25x1,5, for cables Ø 12-17 mm, EMC version
Approvals	
Approvals:	UL + C-UL VDE