



— PRODUCT DATA SHEET

P3



P3



PRODUCT DESCRIPTION

The P3 key-ring torch may be tiny in size but it certainly packs a big punch when it comes to lighting up the dark. The renowned Advanced Focus System allows for easy Spot/Flood focusing and creates the ideal illumination for any range. Fuss-free operation with a single AAA alkaline battery and a high-quality housing made of 75% recycled aluminium round off this handy everyday light. Backed by a 7-year with registration warranty for complete peace of mind.

- Key-ring torch with Spot/Flood focusing function (Advanced Focus System) and three brightness levels
- Operates with a single AAA alkaline battery
- Intuitive operation via End Cap Switch
- Sustainable: Uses 75 % recycled aluminium⁹ and backed by a 7-year warranty*
- Keyring to safely attach the torch to keys or backpack

TECHNICAL DATA	
Weight incl. batteries [g]	43
Material	Aluminum alloy
Length [mm]	94
Length (focused) [mm]	98
Tube diameter [mm]	15
Head diameter [mm]	20
POWER SUPPLY	
Battery quantity	1
Rechargeable	No
Battery type	Alkaline
Total battery voltage [V]	1.5
Total battery capacity [mAh]	0
Total battery energy [Wh]	0 Wh
Useable batteries	AAA NiMH 1.2V
FURTHER SPECIFICATIONS	
IP class	IP54
Drop test (drop height) [m]	2
Working temperature range [°C]	-20 to +40

LIGHT FUNCTIONS			
Cool White Main: Power, Mid power, Low power			
LIGHT SOURCE		MAIN	
Amount LEDs		1	
Colour		Cool White	
Colour temperature [K]		6000 to 7500	
Colour rendering index (CRI)		70	
LIGHT VALUES - Cool White Main			
	Power	Mid power	Low power
Light output [lm]	130	60	20
Beam distance [m]	110	70	40
Run time [h]	2.5	4	6.5
SWITCH			
End-cap Switch			
TECHNOLOGIES			
Advanced Focus System, Rapid Focus			

P3

PACKAGING AND LOGISTICS



For illustration purposes only

PACKAGING INFORMATION	
Type of packaging	Box
Supplied with	1 set of batteries - AAA, Key ring
Item No.	503106
Colour	Black
STERLING RRP inc / ex vat	£26.95 / £22.46
EURO RRP inc / ex vat	€TBC / €TBC
SINGLE PACKAGE	
Dimensions W x H x D [cm]	14.5 x 8.5 x 4.2
Gross weight [g]	98.5
GTIN-13	4058205037228
EXPORT CARTON	
Unit	24
Dimensions W x H x D [cm]	37.5 x 17 x 31
Gross weight [g]	3030
GTIN-13	4058205037204

P3

PRODUCT SERIES

Powerful torches for those who push boundaries—the discerning enthusiasts, the industrious workers, the bold adventurers and the forward-thinkers. Lights that bridge the gap between the epic and the technical. In your hand, they do more than shine—they guide your path, reveal the unknown and empower you to explore, discover and redefine what is possible. Pioneering Brilliance. The P-Series: Redefined.

P3

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

*) 7 year warranty only if registered, otherwise 2 years.
Warranty conditions viewable at <https://ledlenser.com/en/infos-service/warranty/>

1) Measured values according to ANSI/PLATO FL 1 in the respective setting named. If no setting is specifically named, the luminous flux (lumens/lm) and range (meters/m) values refer to the brightest setting and the burn time (hours/h) values refer to the lowest setting. A boost function (if available) can be used several times, but is only available for a short time at a time. In case the lamp is equipped with colored LED(s), the measured values are given with white light or the white LED. If the lamp has different energy modes, the "energy saving mode" is the basis for the measurement.

9) All aluminium components are made of at least 75 % recycled aluminium and may thus vary in surface structure and color.