





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2008
 © COPYRIGHT 2008 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
AL	2	F	New drawing released	10NOV2008	J.S	P.E.G



- Notes:
- 1 Sn over Ni in the crimp zone
 - 2 Gold over nickel in the contact zone
 - 3. For insulation Ø1.0-2.5mm suitable
 - 4 Au over Ni in the wire crimp and contact zones, otherwise 1.3µm Ni



OBSOLETE

1 2	Brass	926895-7
1 2	Phosphor Bronze	926895-6
Pre-tin plated	Phosphor Bronze	926895-3
4	Brass	926895-2
Pre-tin plated	Brass	926895-1
Finish	Material	Part no.
Colour		

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN J. Salo 10NOV2008 CHK R. Sole 10NOV2008 APVD P.F.Grassano 10NOV2008 PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		Tyco Electronics AMP España, S.A. Barcelona, Spain.	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLØ ±- 1 P/C ±0.2 2 P/LC ±- 3 P/LC ±- 4 P/LC ±- ANGLES ±1° 30' FINISH See table		NAME Universal M-N-L socket 0.2-0.8mm ² wire range SIZE A3 CAGE CODE - DRAWING NO ©926895 RESTRICTED TO -	
MATERIAL See table		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1