

### Main

Range of product	Canalis
Product name	KS
Offer type	Complementary
Product or component type	Tee
Busbar description	Standard
Bar material	Aluminium
Device application	Change direction
[Ie] rated operational current	1000 A at 35 °C
Direction change type	Edgewise to perpendicular - neutral to up
Colour	White (RAL 9001)

### Complementary

[Ue] rated operational voltage	230...690 V
Network frequency	50/60 Hz
Operating angle	90 °
Busbar trunking polarity	3L + N + PE
Mounting location	On trunking
Mounting position	Any position
Electrical connection	Lubricated sliding contact
Mounting mode	By screws
Width	113 mm
Height	146 mm
Length	Side 1: 290 mm Side 2: 290 mm Side 3: 290 mm
Net weight	10 kg

## Environment


IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Standards	IEC 61439-6 IEC 60439-2

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------



## Dimensions

KSA1000DTC40

A (mm)	290
B (mm)	290
C (mm)	290
D (mm)	-
Fire barrier	No
Fire barrier position	-