


















2380600-1 AS SHOWN



- 1 DETAILS OF DESIGN ARE LEFT TO TE CONNECTIVITY
- 2 PACKAGING: TAPE AND REEL
- 3 ALL DIMENSIONS IN BRACKETS () FOR INFORMATION ONLY
- 4 SUITABLE MATING PLUG HOUSING ASSEMBLY TE-PN
X-2310137-X, OR PLEASE CONTACT TE
CONNECTIVITY
- 5 CENTER OF GRAVITY
- 6 AREA OF STAND OFF IS OPTIONAL PASTE FOR CUSTOMER



CODINGS, 3:1						
CODING A	CODING B	CODING C	CODING D	CODING E	CODING F	CODING G
						
CODING H	CODING J	CODING K	CODING L	CODING M	CODING Z	
						

1														PICK-UP CAP	NYLON	-	5	
1														CONTACT PIN	COPPER ALLOY	SOLDER SIDE: MIN. 3µm Sn OVER Ni INTERFACE SIDE: MIN. 2µm Ag OVER Ni	4	
1														CAVITY BLOCK	POLYAMIDE	BLACK	3	
1														SHIELDING BODY	Zn ALLOY	MIN. 3µm Sn OVER Ni	2	
												1	Z	CODING COVER	PA10T GF30	WATER BLUE LEAF GREEN PASTEL GREEN CURRY BEIGE HEATHER VIOLET BLUE GREY NUT BROWN MAY GREEN CLARET VIOLET LIGHT BLUE PURE WHITE JET BLACK	1	
												1	M					
													L					
													1					K
																		J
													1					H
																		G
													1					F
																		E
													1					D
																		C
																		B
														A				
1																		
													</					