



HARD DRIVE

EXTERNAL HARD DRIVE / 3.5" / USB 2.0
WIN & MAC



External USB 2.0 Hard Drive

- Fast, low noise external USB 2.0 Hard Drive
- Winner of the iF Product Design Award 2007 for outstanding design!
- Stylish aluminium design, including LED hard drive capacity indicator
- No cooling fan = no noise!
- The easiest way to add extra storage capacity to your computer
- Includes Freecom Backup software for easy file backup
- Hot swappable, no need to turn off your computer
- No device ID's or terminations to worry about
- High quality, sleek design, only 20 x 11,5 x 4 cm
- Two years manufacturers warranty, free helpdesk support

Ideal for home and office use

Home use:

- Store all your digital photo's, music, movies, games on one central location
- Take the Freecom Hard Drive with you and share your files with friends
- Make an extra backup of all your important documents and files
- Make an image of a clean OS installation on your hard drive, easily restore your OS in case of your PC's hard drive crashing

Office use:

- Store all your spreadsheets, documents, presentations on one central location
- Take the drive home or on the road and work on your files away from the office
- Make an extra backup of your valuable work files
- Share data between computers and networks
- Use the Freecom Hard Drive for software installations on multiple PC's.

Stylish and cost-effective external hard drive solution

Today's world is all about Gigabytes. Programs and data take up more and more storage space. The need for installing an extra hard drive on your PC or Mac is more present than ever. Opening your computer case and installing an internal hard drive can be a difficult job. So why not take the easy route? Freecom offers you the perfect storage upgrade for your computer: the new Freecom Hard Drive, a no-nonsense external hard drive in a stylish new design. No need to open your computer; just plug the Hard Drive into the USB (2.0 or 1.1) port of your PC or MAC and you instantly have a substantial increase in storage space. The Freecom Hard Drive is pre-formatted so you're ready to use your drive seconds after connecting it to your computer. At Freecom we create storage solutions from a consumer's perspective, where convenience, design and quality are key factors. Free your mind!

PRODUCT SPECIFICATIONS FREECOM HARD DRIVE:

CAPACITY	250 GB, 400 GB, 500 GB
INTERFACE	USB2.0, can also be connected to USB 1.1 port
HARD DRIVE TYPE	3.5", low noise, low power consumption
PERFORMANCE	Average seek time: > 9 ms Track to Track seek time: 0.8 ms Average Latency: 4.2 ms Rotational Speed: 7200 rpm
HARD DRIVE BUFFER SIZE	250 GB, 400 GB: min. 8MB, 500 GB, min. 16MB
DATA TRANSFER SPEED	over USB 2.0 bus: up to 480Mbit/s
WEIGHT	750 gr. / 26.3 Ounce
DIMENSIONS	20 x 11,5 x 4 cm / 7.9 x 4.5 x 1.6 inch
MTBF	50000 P.O.H.
ENVIRONMENTAL SPECIFICATIONS	Operating temperature: 5° C / 60° C Storage temperature: -20° C / 80° C
MINIMUM SYSTEM REQUIREMENTS	PC: Intel Pentium-III / AMD Duron 700MHz or higher, 128MB RAM, CD-ROM drive, available USB port. Windows 2000/XP MAC: Mac OS X v.10.1 or higher, available USB port

Ref. MM/PW/14-03-2007

PACKAGE INCLUDES:

- Hard Drive (Windows pre-formatted)
- Power Adapter
- USB cable (USB 2.0 & 1.1)
- Freecom Software Media Suite
- Manual on CD & Quick Install Guide
- Free unlimited helpdesk support
- Two years manufacturers warranty

FREECOM SOFTWARE MEDIA SUITE:

Freecom Backup software:	Custom select file extensions; Freecom Backup automatically makes a backup of all files with these extensions.
Freecom Secure & Compress for Windows:	Drag and drop files into folders and these files are crypted and compressed automatically.
Freecom Password protection:	Protects your Freecom Hard Drive with password protection.
Freecom Auto Run for Windows:	Opens files, starts programs automatically if you connect your Freecom Hard Drive to the USB port.
Freecom Sync for Windows:	A synchronization process starts automatically if you connect your Freecom Hard Drive to your computer.

	250 GB	400 GB	500 GB
Art. No. EU/UK	27034 / 27035	27047 / 27048	28604
EAN code EU/UK	4021801270344 / 4021801270351	4021801270474 / 4021801270481	4021801286048
Color	Silver	Silver	Silver