


Order No.: 1766136

Type: GMSTB 2,5/ 3-G-7,62

Header



The figure shows a 10-position version of the product

1 Main features



- | | | | |
|-------------------------|---------------------|------------------------|---------------------|
| • No. of pos. | 3 | • Nominal current | 12 A |
| • Nominal cross section | 2.5 mm ² | • Nominal voltage | 630 V |
| • Color | green | • Connection direction | 0 ° |
| • Pitch | 7.62 mm | • Type of packaging | packed in cardboard |
| • Mounting type | Wave soldering | | |

2 Your advantages

- ✓ Maximum flexibility when it comes to device design – one header for connectors with different connection technologies
- ✓ Items that can be aligned in various pitches support flexible and space-saving PCB assembly
- ✓ Well-known mounting principle allows worldwide use
- ✓ Larger pitch for increased voltage requirements
- ✓ Plug-in direction parallel to the PCB




Make sure you always use the latest documentation.
It can be downloaded at: phoenixcontact.net/product/1766136

3 Table of contents

| | | |
|----|---|----|
| 1 | Main features..... | 1 |
| 2 | Your advantages | 1 |
| 3 | Table of contents | 2 |
| 4 | 3D model in PDF can be activated (Acrobat Reader only)..... | 3 |
| 5 | item properties..... | 4 |
| | 5.1 Material data | 4 |
| 6 | Dimensions..... | 4 |
| | 6.1 Dimensions for the product | 4 |
| | 6.2 Dimensions for PCB design..... | 4 |
| 7 | Series drawing..... | 5 |
| 8 | Packaging information | 5 |
| 9 | Application..... | 5 |
| | 9.1 Temperature limit values | 5 |
| 10 | Mechanical tests..... | 6 |
| 11 | Electrical tests | 7 |
| | 11.1 Electrical data..... | 7 |
| | 11.2 Air and creepage distances | 7 |
| 12 | Current carrying capacity/derating curves | 8 |
| 13 | Environmental and durability tests | 9 |
| | 13.1 Vibration test | 9 |
| 14 | Classification for connectors..... | 9 |
| 15 | Approvals | 9 |
| 16 | Commercial Data..... | 11 |
| 17 | corresponding plugs | 11 |
| 18 | Accessories..... | 11 |
| 19 | Combination tests..... | 12 |

1766136 GMSTB 2,5/ 3-G-7,62

4 3D model in PDF can be activated (Acrobat Reader only)



1766136 GMSTB 2,5/ 3-G-7,62**5 item properties**

| | |
|---------------------|---------------------|
| Order No. | 1766136 |
| Type | GMSTB 2,5/ 3-G-7,62 |
| Type of contact | Male connector |
| Range of articles | GMSTB 2,5/...G |
| Pitch | 7.62 mm |
| Number of positions | 3 |
| Locking | without |
| Mounting type | Wave soldering |
| Pin layout | Linear pinning |

5.1 Material data

| | |
|---|---|
| Material of metal parts | |
| Note | WEEE/RoHS-compliant, whisker-free acc. to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material | Cu alloy |
| Surface contact area | Ni 1 µm ... 3 µm , Sn 3 µm ... 5 µm |
| Soldering area surface | Ni 1 µm ... 3 µm , Sn 3 µm ... 5 µm |
| Surface characteristics | Tin-plated |
| Insulating material data | |
| Insulating material | Housing PA |
| CTI according to IEC 60112 | 600 |
| Flammability rating according to UL 94 | V0 |
| Color | green (6021) |
| Glow wire flammability index GWFI according to EN 60695-2-12 | 850 |
| Glow wire ignition temperature GWIT according to EN 60695-2-13 | 775 |
| Temperature for the ball pressure test according to EN 60695-10-2 | 125 °C |

6 Dimensions**6.1 Dimensions for the product**

| | |
|-----------------------------|----------|
| Length | 12 mm |
| Width | 21.06 mm |
| Height (without solder pin) | 8.6 mm |
| Total height | 11.8 mm |
| Solder pin [P] | 3.2 mm |
| Dimension a | 15.24 mm |

6.2 Dimensions for PCB design

| | |
|----------------|-----------|
| Hole diameter | 1.4 mm |
| Pin dimensions | 1,0 x 1,0 |

1766136 GMSTB 2,5/ 3-G-7,62

7 Series drawing

8 Packaging information

| | |
|--------------------|---------------------|
| Type of packaging | packed in cardboard |
| Pieces per package | 50 |

9 Application

9.1 Temperature limit values

| | |
|---|--|
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Ambient temperature (operation) | -40 °C (dependent on the derating curve) |

1766136 GMSTB 2,5/ 3-G-7,62**10 Mechanical tests**

| Mechanical test group A | |
|-------------------------------------|------------------------|
| Specification | IEC 61984:2008-10 |
| Visual test | Test passed |
| Specification | IEC 60512-1-1:2002-02 |
| Dimensional test | Test passed |
| Specification | IEC 60512-1-2:2002-02 |
| Resistance of marking | Test passed |
| Specification | IEC 60068-2-70:1995-12 |
| Insertion and withdrawal force | Test passed |
| Specification | IEC 60512-13-2:2006-02 |
| No. of cycles | 25 |
| Insertion strength per pos. approx. | 8 N |
| Withdraw strength per pos. approx. | 6 N |
| Polarization and coding | Test passed |
| Specification | IEC 60512-13-5:2006-02 |
| Test force | 20 N |
| Contact retention in insert | Test passed |
| Specification | IEC 60512-15-1:2008-05 |
| Test force per pos. | 39 N |

1766136 GMSTB 2,5/ 3-G-7,62**11 Electrical tests****11.1 Electrical data**

| | |
|---|----------------------------|
| Rated current / conductor cross section | 12 A / 2.5 mm ² |
| Rated insulation voltage (III/2) | 630 V |
| Rated surge voltage (III/2) | 6 kV |
| Contact resistance | 1.6 mΩ |
| Degree of pollution | 2 |


11.2 Air and creepage distances

| | | | |
|---|---------------------|--------|--------|
| Component | Header | | |
| Specification | IEC 60664-1:2007-04 | | |
| Mains type | unearthed mains | | |
| Insulating material group | I | | |
| Comparative tracking index (IEC 60112:2003-01) | CTI 600 | | |
| Rated insulation voltage | 400 V | 630 V | 630 V |
| Rated surge voltage | 6 kV | 6 kV | 6 kV |
| Degree of pollution | 3 | 2 | 2 |
| Overvoltage category | III | III | II |
| Minimum clearance case A (inhomogeneous field) | 5.5 mm | 5.5 mm | 5.5 mm |
| Minimum value of the creepage path requirement in acc. with table | 6.3 mm | 5.5 mm | 5.5 mm |

1766136 GMSTB 2,5/ 3-G-7,62

12 Current carrying capacity/derating curves

| | |
|-------------------------|---|
| Specification | IEC 61984:2008-10 |
| Note | Representation based on IEC 60512-5-2:2002-02 |
| Reduction factor | 0.8 |
| Number of positions | See diagram |
| Conductor cross section | 2.5 mm ² |
| Note | |

Type: FRONT-GMSTB 2,5/...-ST-7,62 with GMSTB 2,5/...-G-7,62


1766136 GMSTB 2,5/ 3-G-7,62**13 Environmental and durability tests****13.1 Vibration test**


| | |
|------------------------|------------------------|
| Specification | IEC 60068-2-6:2007-12 |
| Result | Test passed |
| Frequency | 10 - 150 - 10 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.35 mm (10 - 60.1 Hz) |
| Acceleration | 5 g (60.1 - 150 Hz) |
| Test duration per axis | 2.5 h |
| Test directions | X-, Y- and Z-axis |


14 Classification for connectors


| | |
|-----------------------------------|--|
| Specification | IEC 61984:2008-10 |
| Main features | Connectors without switching capacity (COC) |
| Construction form | Fixed connectors |
| Strain relief elements | without strain relief |
| Protection against electric shock | Not encapsulated - touch-proof when inserted |
| Protection class | |
| Protective conductor | without PE |
| Lock | no |

15 Approvals


| CSA  | | | | |
|---|-------|-------|--|--|
| Use group | B | D | | |
| mm ² /AWG/kcmil | | | | |
| Voltage | 300 V | 300 V | | |
| Current | 10 A | 10 A | | |

| UL Recognized  | | | | |
|---|-------|-------|--|--|
| Use group | B | D | | |
| mm ² /AWG/kcmil | | | | |
| Voltage | 300 V | 300 V | | |
| Current | 15 A | 10 A | | |

| VDE Gutachten mit Fertigungsüberwachung  | | | | |
|---|-------|--|--|--|
| mm ² /AWG/kcmil | | | | |
| Voltage | 400 V | | | |
| Current | 12 A | | | |

| cUL Recognized  | | | | |
|--|-------|-------|--|--|
| Use group | B | D | | |
| mm ² /AWG/kcmil | | | | |
| Voltage | 300 V | 300 V | | |
| Current | 15 A | 10 A | | |

1766136 GMSTB 2,5/ 3-G-7,62


IECEE CB Scheme 

mm²/AWG/kcmil

| | | | | |
|---------|-------|--|--|--|
| Voltage | 400 V | | | |
|---------|-------|--|--|--|

| | | | | |
|---------|------|--|--|--|
| Current | 12 A | | | |
|---------|------|--|--|--|

EAC 

cULus Recognized 

1766136 GMSTB 2,5/ 3-G-7,62**16 Commercial Data**

| | |
|--------------------|--|
| Order No. | 1766136 |
| Type | GMSTB 2,5/ 3-G-7,62 |
| Pieces per package | 50 |
| Net weight | 1.543 g |
| GTIN | 4017918032159 |
| | Information that applies locally, see link on page 1 |
| Country of origin | Information that applies locally, see link on page 1 |

17 corresponding plugs


| Order No. | Type |
|-----------|----------------------------|
| 1767012 | GMSTB 2,5/ 3-ST-7,62 |
| 1806122 | FRONT-GMSTB 2,5/ 3-ST-7,62 |
| 1823079 | GMSTBP 2,5/ 3-ST-7,62 |
| 1832426 | GMVSTBW 2,5/ 3-ST-7,62 |
| 1832536 | GMVSTBR 2,5/ 3-ST-7,62 |
| 1939646 | GFKC 2,5/ 3-ST-7,62 |

18 Accessories

| Description | Order No. | Type |
|---|-----------|--------------------------|
| Coding section, inserted into the recess in the header or the inverted plug, red insulating material | 1734401 | CR-MSTB |
| Keying cap, for forming sections, plugs onto header pin, green insulating material | 1755477 | MSTB-BL |
| Mounting flange, for fixing both ends of the header onto the PCB, green insulating material, with M 2 x 14 screws and nuts. | 1759981 | MSTB-BF |
| | 0804549 | SK 7,62/3,8:FORTL.ZAHLEN |

1766136 GMSTB 2,5/ 3-G-7,62

19 Combination tests

**GMSTB 2,5/..-G****FRONT-GMSTB
2,5/..-ST**

| | | | | |
|--|---|--|--|--|
| Specification | IEC 61984 | | | |
| Mechanical tests (A) | | | | |
| Insertion/withdrawal force per position | approx. 8 N / 6 N | | | |
| Polarization when inserted Requirement >20 N | Test passed | | | |
| Contact holder in insert Requirements >20 N | Test passed | | | |
| Durability tests (B) | | | | |
| Contact resistance R_1 | 1.6 m Ω | | | |
| Insertion/withdrawal cycles | 25 | | | |
| Contact resistance R_2 | 1.6 m Ω | | | |
| Rated impulse voltage at sea level Voltage waveform $\geq (1.2/50 \mu\text{s})$ | 4.8 kV | | | |
| Power-frequency withstand voltage Voltage waveform $\geq (50/60 \text{ Hz})$ | 2.21 kV | | | |
| Insulation resistance Requirements > 5 M Ω | > 0.2 T Ω | | | |
| Thermal tests (C) | | | | |
| Tested number of positions | 12 | | | |
| Tested conductor cross section | 2.5 mm ² | | | |
| Test current | 12 A | | | |
| Upper limiting temperature Requirements < 100°C | Test passed | | | |
| Climatic tests (D) | | | | |
| Test sequence 1: low temperature storage | -40 °C/2 h | | | |
| Test sequence 2: heat storage | 100 °C/168 h | | | |
| Test sequence 3: noxious gas storage (ISO 6988) | 0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle | | | |
| Rated impulse voltage at sea level Voltage waveform $\geq (1.2/50 \mu\text{s})$ | 4.8 kV | | | |
| Power-frequency withstand voltage Voltage waveform $\geq (50/60 \text{ Hz})$ | 2.21 kV | | | |
| Environmental and endurance tests (E) | | | | |
| Specification | IEC 61984:2008-10 | | | |
| Degree of protection | Finger safety with IP20 test finger | | | |