


FEATURES

- **High Chemical Resistance:** Suitable for use with a wide range of chemicals, enhancing versatility.
- **Temperature Range -20 °C to 140 °C:** Operates effectively in extreme temperatures, ensuring reliability.
- **Shore A Hardness 90 to 95:** Provides a balance of flexibility and strength for optimal sealing.
- **Durable Materials:** Constructed from Fluorinated Ethylene Propylene and Viton for enhanced longevity.
- **Precision Fit:** Inside diameter of 72.39 mm and outside diameter of 83.05 mm for secure sealing.

RS PRO 72.39 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-387



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in various industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene and Viton, it offers excellent resistance to chemicals and high temperatures. Ideal for use in environments where durability and performance are critical, this O-Ring Seal ensures a secure fit and long-lasting service.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	72.39 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	83.05 mm
Thickness	5.33 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

