



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Dust Cap**
Number of Positions: **64**
Operating Temperature (Max): **105 °C [221 °F]**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

| | |
|----------------------|----------|
| Connector Cover Type | Dust Cap |
|----------------------|----------|

Configuration Features

| | |
|---------------------|----|
| Number of Positions | 64 |
|---------------------|----|

Housing Features

| | |
|---------------------------------|----------|
| Compatible With Connector Shape | D-Shaped |
|---------------------------------|----------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature (Max) | 105 °C[221 °F] |
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |

Packaging Features

| | |
|--------------------|---------|
| Packaging Method | Package |
| Packaging Quantity | 1 |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) |



| | |
|---------------------------|-------------------------------------------------------------------------------------|
| | Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 229969-2
COVER, DUST, RCPT, RED, CHAMP


Also in the Series | CHAMP Docking Connectors



Connector Caps & Covers(29)




Connector Hardware(28)



Connector Strain Relief(2)




Docking Connectors(19)




IDC D-Sub Connectors(55)

Customers Also Bought



TE Part #229975-1
ASSY,RCPT,50POS,B SLOT,BLK HSG



TE Part #552488-1
ASSY, PLUG, 64 POS, E SLOT



TE Part #552008-1
KIT, COVER, 180, 50 POS



TE Part #229974-1
ASSY, PLUG, 50 POS, B SLOT




TE Part #229969-1
COVER,DUST,RCPT,RED,CHAMP




TE Part #1-745496-7
25 HDE MS PLUG,22-26,LEAD FREE




TE Part #4-552008-1
KIT, COVER, 180, 50 POS



TE Part #5-104505-5
MTE PIN LP



TE Part #229910-1
CLAMP, CABLE "CHAMP PACKAGING"



TE Part #229909-1
COVER,TAPERED,90DEG"CHAMP PKG"

Documents

Product Drawings

COVER, DUST, PLUG, BLUE, CHAMP

English

CAD Files

Customer View Model

ENG_CVM_CVM_229968-2_Z.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_229968-2_Z.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_229968-2_Z.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.