

Eaton 072333

Catalog Number: 072333

Eaton Moeller® series RMQ16 Illuminated selector switch actuator, maintained/momentary, 45°, 18 x 18 mm, 3 positions, With thumb-grip, green, with VS anti-rotation tab, without light elements, With base, W2x4,6d; max. 30 V Q18LWK3R2-GN

General specifications

Product Name

Eaton Moeller® series RMQ16
Illuminated selector switch actuator

Catalog Number

072333

EAN

4015080723332

Product Length/Depth

75 mm

Product Height

18 mm

Product Width

18 mm

Product Weight

0.014 kg

Certifications

IEC/EN 60947-5
UL
UL Category Control No.: NKCR
CE
UL 508
UL File No.: E29184
CSA
CSA Class No.: 3211-03
CSA-C22.2 No. 14-05
IEC/EN 60947
CSA File No.: 46552

Catalog Notes

Filament bulb or LED needs to be
ordered separately



Product specifications

Type

Illuminated selector switch actuator

Actuator color

Black

Actuator function

Maintained/momentary

Switching function latching

Spring-return

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Please enquire

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

Resources

Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004158.pdf](#)

[DA-DC-00004136.pdf](#)

Drawings

[eaton-operating-switch-rmq16-dimensions.eps](#)

[eaton-operating-button-symbol-004.eps](#)

eCAD model

[DA-CE-ETN.Q18LWK3R2-GN](#)

Installation instructions

[IL04716016Z](#)

mCAD model

[leuchtwahl_18.stp](#)

[DA-CD-wahl_18](#)

[DA-CS-wahl_18](#)

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

VS anti-rotation tab

Operating frequency

1800 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Connection to SmartWire-DT

No

Actuator type

Toggle

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

25 °C

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Opening diameter

16 mm

Opening height

0 mm

Operating torque

0.2 Nm

Rated insulation voltage (U_i)

250 V

Rated operational current for specified heat dissipation (I_n)

0 A

Rated operational voltage (U_e) at AC - max

24 V

Static heat dissipation, non-current-dependent P_{vs}

0 W

Switching angle

45 °

Width opening

0 mm

Rated impulse withstand voltage (U_{imp})

800 V AC

Bezel color

Black

Shock resistance

Mechanical, According to IEC/EN 60068-2-27

40 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal

shock 11 ms

Bezel material

Plastic

Terminal capacity

0.5 - 1.0 mm²

Design

With thumb-grip

Mounting position

As required

Terminal size

2.8 x 0.8 mm to DIN 46247 and IEC 60760, Fast-on connectors

2.8 x 0.8 mm to DIN 46244, Blade terminal

Overvoltage category

III

Control circuit reliability

1 failure per 10,000,000 switching operations (Statistically determined, at 24 V DC/5 mA)

1 failure per 5,000,000 switching operations (statistically determined, at 5 V DC/1 mA)

Degree of protection

NEMA 1

Degree of protection (front side)

IP65

Indicator color

Green

Lens type

Square

Lifespan, mechanical

3,000,000 Operations

Number of switch positions

3

Size

Front dimensions: 18 x 18 mm

Product category

RMQ16

Suitable for

Illumination



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)